



NETpodium Back Panels (1-1671579-1/1-1671579-2)

INSTRUCTION SHEET 411-117005 FEB 2017 REV B


1. Kit content

Back panel left 1 pc
Back panel right 1 pc
Back strip (included with 1-1671579-2) 1 pc
Assembly hardware


2. NETpodium aluminum profile




3. Install Back Panel Left




Place the positioning bracket at the bottom of the back panel in the horizontal groove of the NETpodium profile.



Make sure that the back panel is positioned in front of the installed bracket.



Place the rotating bracket in horizontal position.



Slide the back panel to the right and insert the positioning brackets on the side of the back panel into the vertical groove of the NETpodium profile.

NETpodium Back Panels (1-1671579-1/1-1671579-2)

INSTRUCTION SHEET 411-117005 FEB 2017 REV B




Turn the rotating bracket a quarter into the horizontal groove of the NETpodium profile.

4. Install Back Panel Right



Place the positioning bracket at the bottom of the back panel in the horizontal groove of the NETpodium profile.



Slide the back panel to the left and insert the positioning brackets on the side of the back panel into the vertical groove of the NETpodium profile.



Use an Allan key n°5 with conical head to fix the back panels with screws and washers (torque of 3.5-4Nm).



The back panels need to be fixed in these 5 positions.

NETpodium Back Panels (1-1671579-1/1-1671579-2)

INSTRUCTION SHEET 411-117005 FEB 2017 REV B

5. Install the Back Strip (included with PN 1-1671579-2)



Use an Allan key n°5 with conical head to fix the back strip with screws and washers (torque of 3.5-4Nm).



The back strip needs to be fixed at these 2 positions.

Install a back strip to close the gap between two NETpodium racks installed side by side.

INSTRUCTION SHEET

Contact us:

Technical Support
Technical Assistance Center (TAC)
Tel.: 800-830-5056
Email: TAC.Americas@commscope.com
www.commscope.com

COMMSCOPE®

While CommScope has made every reasonable effort to ensure the accuracy of the information in this document, CommScope does not guarantee that it is error-free, nor does CommScope make any other representation, warranty, or guarantee that the information is accurate, correct, reliable, or current. CommScope reserves the right to make any adjustments to the information contained herein at any time without notice. CommScope expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult CommScope for the latest dimensions and design specifications.

To obtain information on CommScope® products, visit our website at <http://www.commscope.com/SupportCenter>.

This product is covered by one or more U.S. patents or their foreign equivalents. For patents, see www.commscope.com/ProductPatent/ProductPatent.aspx.

©2017 CommScope, Inc. All Rights Reserved 411-117005