		8	7 6		5	+	4		3	2	1		
IT	ΓEΜ	PART NO.	DESCRIPTION	QTY.	WEIGHT				REV. ZONE	REVISIONS DESCRIPTION	BY	DATE	
	1	LSA	Small to large adapter halve	2	8.27 LBS				A ZONE	INITIAL RELEASE		DATE 02/29/00	
	2	LCP10	LARGE CLAMP HALF	2	7.07 LBS				В	REVISED & REDRAWN		03/22/01	
	3	MT-382-18	5/8" X 18" THREADED ROD	4	1.45 LBS								
	4	GWF05A	5/8" GALV FLAT WASHER (A325)	8	0.03 LBS		(2)						
	5	GWL-05	5/8" GALV LOCK WASHER	8	0.01 LBS								D
	6	GN05A	5/8" GALV HEX NUT (A325)	8	0.08 LBS								IJ
	7	GB-0416A	1/2" X 1-3/4" GALV BOLT KIT (Å325)	4	0.15 LBS			= 1		<			
	8	GWF04A	1/2" GALV FLAT WASHER (A325)	8	0.02 LBS								
	- 1					/							
							Y						
_							/					-	
										T SIO			
					$   \leq    \leq    \leq    \leq    \leq    \leq    \leq    $	$\leq$							
					$\downarrow$								
С										TATIO			С
							$\sim$						
						/							
				/	$\neg \frown \frown$	$\sim$ /				1 mil			
				(	6 ( 5 ( 4 )	3)—⁄		$\mathbf{v}$	$\sim$				
								Ø					
							$\checkmark$						€
								= 1					
						/							
							/						
B							<i>,</i>						В
													IJ
					~ //								
					YR ~	Y				// //			
					$\parallel$	$\boldsymbol{\boldsymbol{\smallsetminus}}$							
					$\bigvee$	$\overline{\}$							
										FATTOR			
$\neg$							$\sim$					-	-
									E C	T B			
										$\downarrow$ $\frown$ $\frown$			
								2		( 7 ) 8	; )		
								Ð					
A							These drawings and specification property of ANDREW CORPORATIO	ns are the proprietary ON and may be used	ACG 1	of 1 PART NUMBER LS-SB50			А
							Andrew Corpora	ration.	CHECKED BY: SCALE:	DESCRIPTION:			
							ALL DIMENSIONS ARE IN INCHES U TOLERANCES UNLESS OTHERWISE SF		TP NTS	ADAPTER CLAMP SET, 8" O.D. TO DRAWING TYPE:	16° U.D.		
								GLES ± 2° ACTIONS ± 1/3	09/28/05 A36				
							.XXX= ± .010		REVISION: FINISH: GAL	V A123			
							REMOVE BURRS AND BREAK EDG		B WEIGHT		ORLAND PARK, II	L. 0U462	
		8	7 6		 	ŕ	DO NOT SCALE T	I HIS PRINT	38.5				
		0	· / b	I	Ĵ	I	4		J	·	1		



