

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © 2016 Commscope, INC. Confidential NOTICE: These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
C		ECN8000019319 - REBRANDING	22DEC2016	CY	JS		



**NOTES:**

- 1 ATTENUATION  $\leq 0,3\text{dB}$ , MEASURED AGAINST REFERENCE CONNECTOR
- 2 RETURN LOSS  $\geq 45\text{dB}$ , IN MATED CONDITION
- 3 TUNED CONNECTOR
- 4 INFORMATION ON LABEL IN BAG:
  - UNIQUE SERIAL NUMBER
  - COMMSCOPE PART NUMBER
  - PO NUMBER
  - ATTENUATION AND RETURN LOSS AT 1310nm
- 5 CABLE INFORMATION:
  - CORE DIAMETER:  $9/125\mu\text{m}$
  - OUTER JACKET DIAMETER: 0,9mm
  - OUTER JACKET COLOUR: WHITE
  - OUTER JACKET MATERIAL: HYTREL

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850

PART NUMBER	"L" (meter)
X-6695512-Y	XY,0

Qty	Description	Item
1	FOAC INFORMATION LABEL	-
1	LC CONNECTOR, ONE PIECE, SINGLE MODE, BLUE	2
L	FOCAB 0,9T 9/125, WHITE HYTREL	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 01AUG2007	<b>COMMSCOPE, INC.</b>	
DIMENSIONS: mm		CHK A. HENGELMOLEN 10AUG2007		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. HENGELMOLEN 10AUG2007	NAME -	
0 PLC ± -		PRODUCT SPEC	FOSM PIGTAIL 0,9T LC/PC TUNED	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± -		WEIGHT	SIZE A2	CAGE CODE -
3 PLC ± -		FINISH	DRAWING NO C=6695512	RESTRICTED TO -
4 PLC ± -			SCALE NTS	SHEET 1 of 1
ANGLES ± -			REV C	
MATERIAL -			CUSTOMER DRAWING	

6695512