

# VIP4402W

# Compact Mediaroom<sup>®</sup> IPTV, HEVC, HD Set-Top with 802.11ac Wi-Fi

### **FEATURES**

- Compact HD Client STB
- Broadcom 7250, 6000 DMIPS SOC
- HEVC support
- Available in multiple bottom cover colors
- Optional 802.11ac 2x2 Wi-Fi for high quality IPTV applications
- Universal Remote Control friendly, supports IR and BLE options
- DDR4-2400 DRAM

#### **PRODUCT OVERVIEW**

Introducing the new generation of HEVC capable IP set-top boxes in stylish casing design. The VIP4402W delivers stunning high definition video viewing experience in a beautiful small 5" round chassis. 802.11ac 2x2 Wi-Fi connectivity ensures high quality IPTV delivery with an exceptional ease of installation.





SPECIFICATIONS	
Processing	
CPU	6k DMIPS
DRAM	1GB DDR4-2400
Flash	1GB NAND
Video Interfaces	
Digital video	HDMI with HDCP
Analog video	CVBS in 3.5mm TRRS
Video codecs	HEVC 1080p60 10-bit MPEG-4 AVC (H.264) HP@L4.2 1080p60, MPEG-2 (Optional subject to separate license). Other codecs on request
Video Output	
High definition	720p, 1080i, 1080p60
Graphics	OpenGL 3.0,2.0, 1.1 / 1 Gpix/s
Audio Interfaces	
Digital audio	Optical in A/V 3.5mm
Analog audio	R + L in A/V 3.5mm
Audio codecs	EAC3, MPEG-1 (MUSICAM), MP3, AAC LC, HE-AAC. Other codecs on request
Other Interfaces	
Ethernet	GPHY - Gigabit Ethernet port
Wi-Fi	802.11ac 2x2
Remote control support	IR 36 or 38 kHz, with BLE
USB	1 x 2.0
Status LED	Dynamic array

## SPECIFICATIONS (CONTINUED)

95 cm
1.5A) meets DoEv6
m, fully equipped
o 104ºF)
idensing)
th Dual Boot
MPEG-4/H.264 IEVC Advance, IE-AAC/AAC+, Dolby hrough, Dolby Digital

#### **CUSTOMER CARE**

Contact Customer Care for product information and sales:

United States: 866-36-ARRIS

• International: +1-678-473-5656





HDMI, the HDMI logo and High-Definition Multimedia Interface are trademarks or registered trademarks of HDMI Licensing LLC. Dolby, Dolby Audio, and the double-D symbol are trademarks or registered trademarks of Dolby Laboratories.

VIP4402W-IP-STB

(rev 10-2016)

Note: Specifications are subject to change without notice. Copyright Statement: @ARRIS Enterprises, LLC, 2016. All rights reserved. No part of this publication may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from ARRIS Enterprises, LLC ("ARRIS"). ARRIS reserves the right to revise this publication and to make changes in content from time to time without obligation on the part of ARRIS to provide notification of such revision or change. ARRIS and the ARRIS logo are registered trademarks of ARRIS Enterprises, LLC. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks or the names of their products. ARRIS disclaims proprietary interest in the marks and names of others. The capabilities, system requirements and/or compatibility with third-party products described herein are subject to change without notice.