

# 760053199 | KIT-CLEANING/INSPECT



Cleaning and Inspection Kit, Fiber Optic

OBSOLETE

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cleaning and inspection kit

## General Specifications

Compatible Interface	LC   MPO   SC
----------------------	---------------

## Packaging and Weights

Included	Carrying case   Fiber cleaning solution, 3 oz   Forty cleaning swabs, 1.25 mm   Forty cleaning swabs, 2.5 mm   HD4i Digital Display   Instruction sheet   LC Bulkhead Probe Tip   LC Duplex FMAE Series Probe Adapter   LC I.B.C.   LC and SC Simplex Couplers   MPO coupler, aligned-keys   MTP/MPO Bulkhead Probe Tip   MTP/MPO I.B.C.   One slot reel cleaner   P5000i inspection probe with universal 2.5mm tip and barrel assembly for FBP and FiberChek Probes   SC Bulkhead Probe Tip   SC I.B.C.   Universal 1.25mm Patch Cord Tip   Universal Flare Adapter for FMAE Probe Aadapters   VFL with 1.25 mm and 2.5 mm Adapter Caps
----------	--

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



# 760053199 | KIT-CLEANING/INSPECT

---

## Included Products

- |           |   |   |
|-----------|---|---|
| 1918803-1 | – | One slot reel cleaner for 1.25 mm and 2.5 mm ferrule connectors, MPO/MTP without pins (female), and MT-RJ without pins (female) |
| 1918809-1 | – | Fiber Optic MTP/MPO IBC (In Bulkhead Cleaner)   |
| 2064499-1 | – | Fiber Optic SC IBC (In Bulkhead Cleaner)  |
| 2064500-1 | – | Fiber Optic LC IBC (In Bulkhead Cleaner)  |
| 760249056 | – | Fiber Optic Visual Fault Locator with 2.5 and 1.25 mm Adapter Caps, for connectors such as SC, ST, FC, LC and MU                |



One slot reel cleaner for 1.25 mm and 2.5 mm ferrule connectors, MPO /MTP without pins (female), and MT-RJ without pins (female)

- Handles more than 400 cleanings per cleaner

Product Classification

Regional Availability	Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cleaning kit

General Specifications

Color	Blue
Compatible Connector Type	FC   LC   MPO (female)   MT-RJ (female)   SC   ST

Dimensions

Height	83 mm   3.268 in
Width	48 mm   1.89 in
Length	127 mm   5 in

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

# 1918803-1

---





Fiber Optic MTP/MPO IBC (In Bulkhead Cleaner)

- Cleans male or female MTP/MPO connectors
- Handles more than 400 cleanings per cleaner

Product Classification

Regional Availability	Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cleaning kit

General Specifications

Color	Blue
-------	------

Dimensions

Height	56.5 mm   2.224 in
Width	22 mm   0.866 in
Length	184.2 mm   7.252 in

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





Fiber Optic SC IBC (In Bulkhead Cleaner)

- Simple pushing motion to engage tool
- Audible CLICK to alert the operator when tools is fully engaged
- Dry cleaning strand eliminates the need for solvents to be effective
- Over 525+ engagements per unit

Product Classification

Regional Availability	Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cleaning kit

General Specifications

Color	Blue
Interface	SC

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted





Fiber Optic LC IBC (In Bulkhead Cleaner)

Product Classification

Regional Availability	Australia/New Zealand   Latin America   North America
Portfolio	NETCONNECT®
Product Type	Fiber cleaning kit

General Specifications

Color	Blue
Interface	LC

Dimensions

Height	17.5 mm   0.689 in
Width	17.5 mm   0.689 in
Length	181 mm   7.126 in

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





Fiber Optic Visual Fault Locator with 2.5 and 1.25 mm Adapter Caps, for connectors such as SC, ST, FC, LC and MU

- Locate sharp bends, breaks, and damages in fiber
- Conduct end-to-end continuity tests
- Perform fiber tracing and identification
- Compact, ergonomic design for ultimate portability
- Visible wavelength is 650 nm
- High powered laser (1 mW) for single-mode (> 7 km) and multi-mode (> 5 km) connectors
- Continuous or Flash illumination
- 2.5 mm and 1.25 mm connector inputs

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   North America
Portfolio	CommScope®
Product Type	Tool kit

General Specifications

Compatible Connector Type	FC   LC   SC   ST
---------------------------	-------------------

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Included	2 AAA Batteries   Pouch   VFL with 1.25 mm and 2.5 mm Adapter Caps
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

