

Cluster Support Bracket, u-bolt for 2-3/8 in OD round member attachment

Product Classification

Product Type	Cluster Support Bracket
General Specifications	


Cable Runs, quantity	7
Hole, quantity	7
Mounting	Cluster support
Dimensions	
Height	127 mm 5 in
Width	228.6 mm 9 in
Length	152.4 mm 6 in
Pipe Outer Diameter	60.96 mm 2.4 in
Hole Size	3/4 in 7/16 in

Page 1 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included

Packaging quantity

1

Brackets

Weight, net 1.8 kg | 3.968 lb

Regulatory Compliance/Certifications

Agency

Classification

Page 2 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

CS-B-2

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Included Products

ACS-12	_	Antenna and RRU Cable Support Bracket for up to 12 Cables
CS-B	-	Cluster Support Bracket
GUB-4240	-	Galvanized U-bolt Assembly, 1/2 in x 2-1/2 in x 4 in
PG-CS08	_	PIM-Guard® Antenna and RRU Cable Support Bracket with 8 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.For patents, see www.cs-pat.com
PG-CS23	_	PIM-Guard® Antenna and RRU Cable Support Bracket with 23 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com
PG-CSEB17	-	PIM-Guard® Expansion Bracket - expands PG-CS08 Cable Support Bracket to 23 Ports. For patents, see www.cs-pat.com
PG-RM06	-	PIM-Guard® Round Member Cable Support Bracket 6 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 5 to 7 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com
PG-RMBH12	_	PIM-Guard® Round Member Cable Support Bracket for Block Hangers - Two 3/8" threaded rods for up to 12 hangers. Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.
PG-RMBH12-BP	_	PIM-Guard® Round Member Cable Support Bracket for Block Hangers (pkg of 10)- Two 3/8" threaded rods for up to 12 hangers. Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.

