# UHVMXUCAM

**Base Product** 



Ultra Low Loss (ULL) Multimode OM5 MPO12 (Pinned) to Unconnectorized, Armored Pre-terminated Trunk Cable, 144-Fiber, Plenum

### Product Classification

Regional Availability	Asia   Australia/New Zealand   Europe   Latin America   Middle East /Africa   North America		
Portfolio	CommScope®		
Product Type	Fiber trunk cable assembly		
Product Brand	SYSTIMAX ULL		
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration		

### General Specifications

Connector A, quantity	12		
Color, boot A	Black		
Color, connector A	Lime green		
Connector B, quantity	0		
Color, boot B	Black		
Color, connector B	Lime green		
Construction Type	Armored   Stranded		
Furcation Color	Lime green		
Interface, Connector A	MPO-12/UPC Male		
Interface Feature, connector A	Pinned		
Interface, Connector B	Unterminated		
Jacket Color	Lime green		
Polarity	Method B Enhanced (ULL)		
Fibers per Subunit, quantity	12		
Total Fibers, quantity	144		

### Dimensions

Page 1 of 2


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 11, 2024



# UHVMXUCAM

Breakout Length	33 in
Cable Assembly Length Range (m)	3 – 999
Cable Assembly Length Range (ft)	10 - 999

## Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 °   4.40 lb @ 90 °
Optical Specifications	
Fiber Mode	Multimode   Multimode
Fiber Type	OM5, LazrSPEED®

#### **Environmental Specifications**

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)		
Environmental Space	Indoor   P	Indoor   Plenum	
Included Products			
760230268 P-144-MZ-5G-F12LM		e, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with ultimode OM5, 144 fiber multi-unit with 12 fiber subunits, Lime-green jacket marking	
860617240	- MP012, ULTRA L	OW LOSS, MALE, OM5, LIME, 3mm	

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 11, 2024

