

SSC-760249586X1 | Radio Enclosure MV2



Future Ready Middle of the Pole Concealment for Samsung, Nokia, and Ericsson equipment

- Intended to be used with high powered remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

SSC-760249586E1x Ericsson
SSC-760249586N1x Nokia
SSC-760249586S1x Samsung
*"X" is placeholder for color

Includes mounting hardware for clamp on, through-bolt, or banding to poles or structures.

Available After Market Kits -- ordered separately:

- 860661823S-xx Wood Pole 5" Standoff
- 860661823ST-xx Round Tapered Pole 5" Standoff
- 860661736-MV2-C01x Ice Canopy
- 860661736-MV2-C02 Delta 3.0 rectifier mount kit
- 860661736-MV2-C03 Dual Samsung 320W mount kit
- 860661736-MV2-C07 Nokia AZHL & APAM PSU

Product Classification

Portfolio	CommScope®
Product Type	Mid pole
Product Brand	Metro Cell
Ordering Note	CommScope® standard product with terms
Warranty	One year

General Specifications

Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Power Supply Compatibility	ABB CC1600 APAM CCI PSU-1200W-48-N DELTA 2.0 DELTA 3.0 PSU-AC-08

SSC-760249586X1 | Radio Enclosure MV2

Radio Compatibility, Ericsson	220x 440x 4415 4426 4449 4455 4478 8843 8863
Radio Compatibility, Nokia	AHBCA AHBCC AHFIA AHFIB AHFIC AHLBA AHLBBA AWHQN AZHL
Radio Compatibility Samsung	RF4402D-D1A RFV01U-D1A RFV01U-D2A RT2201-46A RT4401-48A
Radios Included	None

Dimensions

Height	1,219.2 mm 48 in
Width	609.6 mm 24 in
Depth	635 mm 25 in

Electrical Specifications

Power/Fiber Input	Trade size knockouts at rear side
--------------------------	-----------------------------------

Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Aluminum Steel

Environmental Specifications

Thermal Compliance	GR-487
---------------------------	--------

Packaging and Weights

Volume	0.49 m ³ 17.3 ft ³
Weight (loaded)	215.456 kg 475 lb
Weight (unloaded)	31.751 kg 70 lb

* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
-----------------	--