


EQ-P1010-DF



Equipment Platform, 10 ft x 10 ft, base with twelve displacement legs

Product Classification

Product Type Equipment platform system

General Specifications

Legs, quantity 12

Dimensions

Height 546.1 mm | 21.5 in

Width 3048 mm | 120 in

Length 3048 mm | 120 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Load Capacity Up to 10,000 lb (4536 kg) loading

Packaging and Weights

Included Frame | Grating | Hardware | Legs

Packaging quantity 1

Weight, net 850 kg | 1,873.927 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

- EQ-P-DF
- Weight Disbursement Leg for Equipment Platform

EQ-P1010-DF

EQ-P1010-B – Equipment Platform, 10 ft x 10 ft, base only

EQ-P-DF



Weight Disbursement Leg for Equipment Platform

Product Classification

Product Type	Equipment platform system
Ordering Note	ANDREW® standard product (Global)

Dimensions

Height	538.48 mm 21.2 in
Width	393.7 mm 15.5 in
Length	393.7 mm 15.5 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Packaging and Weights


Included	Legs
Packaging quantity	1
Weight, net	15.3 kg 33.731 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



EQ-P1010-B



Equipment Platform, 10 ft x 10 ft, base only

Product Classification

Product Type Equipment platform system

General Specifications

Legs, quantity 0

Dimensions

Height 203.2 mm | 8 in

Width 3048 mm | 120 in

Length 3048 mm | 120 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Load Capacity Up to 10,000 lb (4536 kg) loading

Packaging and Weights

Included Frame | Grating | Hardware

Packaging quantity 1

Weight, net 712.2 kg | 1,570.13 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

