# EQ-P1015-DF



Equipment Platform, 10 ft x 15 ft, base with sixteen displacement legs

#### **Product Classification**

**Product Type** Equipment platform system

#### General Specifications

Legs, quantity 16

#### Dimensions

 Height
 546.1 mm | 21.5 in

 Width
 3048 mm | 120 in

 Length
 4,572 mm | 180 in

#### Material Specifications

Material Type Hot dip galvanized steel

#### Mechanical Specifications

**Load Capacity** Up to 10,000 lb (4536 kg) loading

## Packaging and Weights

Included Frame | Grating | Hardware | Legs

Packaging quantity 1

**Weight, net** 1,186.4 kg | 2,615.561 lb

# Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

EQ-P-DF – Weight Disbursement Leg for Equipment

Platform



# EQ-P1015-DF

EQ-P1015-B

- Equipment Platform, 10 ft x 15 ft, base only

# EQ-P-DF



### Weight Disbursement Leg for Equipment Platform

#### **Product Classification**

**Product Type** Equipment platform system

Ordering Note ANDREW® standard product (Global)

#### **Dimensions**

 Height
 538.48 mm | 21.2 in

 Width
 393.7 mm | 15.5 in

 Length
 393.7 mm | 15.5 in

#### Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

Included Legs
Packaging quantity 1

**Weight, net** 15.3 kg | 33.731 lb

# Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value


ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted





# EQ-P1015-B



# Equipment Platform, 10 ft x 15 ft, base only

#### **Product Classification**

**Product Type** Equipment platform system

#### General Specifications

Legs, quantity 0

#### **Dimensions**

 Height
 203.2 mm | 8 in

 Width
 3048 mm | 120 in

 Length
 4,572 mm | 180 in

#### Material Specifications

Material Type Hot dip galvanized steel

#### Mechanical Specifications

**Load Capacity** Up to 10,000 lb (4536 kg) loading

### Packaging and Weights

Included Frame | Grating | Hardware

Packaging quantity 1

**Weight, net** 1,002.5 kg | 2,210.132 lb

# Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

