MT-219



Pipe Mount Kit, 2-3/8 in OD x 48 in

Product Classification

Product Type

Pipe mount kit

General Specifications

Mounting Pipe, 88.9 mm (3-1/2 in) OD 1

Pipe, quantity

Dimensions

Height	1,219.2 mm 48 in
Width	127 mm 5 in
Length	127 mm 5 in
Pipe Length	1,219.2 mm 48 in
Pipe Outer Diameter	60.96 mm 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included	Crossover bracket Plain end pipes U-bolts
Packaging quantity	1
Weight, net	11.9 kg 26.235 lb

Regulatory Compliance/Certifications

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this guality management system

Included Products

Agency

Pipe Mount Kit - 2-3/8" TO 3-1/2" PIPE - pipe not MT-219-H

Page 1 of 5



MT-219

included

MT-650

Plain End Pipe, 2-3/8 in OD x 48 in .120" A500C 46Ksi _



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

MT-219-H



Pipe Mount Kit - 2-3/8" TO 3-1/2" PIPE - pipe not included

Product Classification	
Product Type	Pipe mount kit
General Specifications	
Mounting	Pipe, 60.3 mm (2-3/8 in) OD Pipe, 88.9 mm (3-1/2 in) OD
Dimensions	
Height	254 mm 10 in
Width	127 mm 5 in
Length	127 mm 5 in
Mounting Diameter, maximum	88.9 mm 3.5 in
Mounting Diameter, minimum	60.325 mm 2.375 in
Material Specifications	
Material Type	Hot dip galvanized steel

Packaging and Weights

Included	Crossover bracket U-bolts
Packaging quantity	1
Weight, net	4.9 kg 10.803 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

an Amphenol company

Page 3 of 5





Page 4 of 5



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

MT-650



Plain End Pipe, 2-3/8 in OD x 48 in .120" A500C 46Ksi

Product Classification

Product Type

Plain end pipe

1

General Specifications

Pipe, quantity

Dimensions

Height	60.96 mm 2.4 in
Width	60.96 mm 2.4 in
Length	1,219.2 mm 48 in
Pipe Length	1,219.2 mm 48 in
Pipe Outer Diameter	60.96 mm 2.4 in
Material Thickness	3.048 mm 0.12 in

Material Specifications

Material Type	A500	Hot dip galvanized steel
Material Grade	С	
Material Strength	46 KSI	

Packaging and Weights

Included	Pipe
Packaging quantity	1
Weight, net	5 kg 11.023 lb

Regulatory Compliance/Certifications

Classification

ISO 9001:2015

Agency

Designed, manufactured and/or distributed under this quality management system

Page 5 of 5

