# **UHVMXMXCK**

#### **Base Product**



Ultra Low Loss (ULL) OM5 MPO12 UPC (pinned) to MPO12 UPC (pinned) Fiber Trunk Cable Assembly, 72-Fiber, Armored Indoor Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

**Ordering Note**For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Connector A, quantity 6

Color, boot A Black

Color, connector A Lime green

Connector B, quantity 6

Color, boot B Black

Color, connector B Lime green

Construction Type Armored | Stranded

Furcation Color Lime green

Interface, Connector A MPO-12/UPC Male
Interface, Connector B MPO-12/UPC Male

Jacket Color Lime green

**Polarity** Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 72

**Dimensions** 

Breakout Length 22 in




# **UHVMXMXCK**

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

## Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 \degree | 4.40 \text{ lb} @ 90 \degree$ 

Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED®

**Environmental Specifications** 

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**COMMSCOPE®** 

# **UHVMXMXCK**

#### Environmental Space Indoor | Plenum

### Regulatory Compliance/Certifications

Agency Classification

ANATEL Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

760242135 – Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with P-072-MZ-5G-F12LM/20T plenum jacket, Multimode OM5, 72 fiber multi-unit with 12 fiber subunits, Lime-green jacket

color, Feet cable marking

860659008 – MPO12, ULL, MALE, OM5, LIME, 2MM

affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names,

trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2025

