SFG23-10-4-126



G23 High Capacity Sector Frame, 10.5 ft face, includes four 126 in pipes; For patents, see www.cs-pat.com

OBSOLETE

This product was discontinued on: March 22, 2023		
Replaced By:		
SFG23HDX-10-4-126	G23HDX High Capacity Sector Frame, 10.5 ft x 2.88 in OD face pipes, includes four 2.88 OD 126 in antenna pipes	

Product Classification

General Sp	ecifications

Product Type

High capacity Tower sector frame

Application4G LTE antenna/radio mountMountingAngle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) ODPatent NumberPatent pendingPipe, quantity4Tower TaperNon-tapered | Tapered

Dimensions

Height	3,200.4 mm 126 in
Face Width	3.2 m 10.5 ft
Width	3,200.4 mm 126 in
Pipe Length	3,200.4 mm 126 in
Face Support Pipe Diameter	60.325 mm 2.375 in
Mounting Diameter, maximum	218.44 mm 8.6 in
Mounting Diameter, minimum	38.1 mm 1.5 in
Pipe Outer Diameter	60.325 mm 2.375 in
Stand-off Distance	1,226.82 mm 48.3 in


Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

SFG23-10-4-126

Outline Drawing



Material Specifications

Material Type Hot dip

Hot dip galvanized steel

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222-G

Packaging and Weights

Included	Frame Pipe mounts Plain end pipes (4) Stiff arm Tower attachment
Packaging quantity	1
Weight, net	378.296 kg 834 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating BWS-Base Wind Speed; FBC-Florida Building Code

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025