

SYSTIMAX 360™ iPatch® G2-1U-MOD LC 5PK imVision Upgrade Kit



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Upgrade kit
Product Brand	SYSTIMAX 360™ iPatch®

General Specifications

Color	Cool gray
Intelligence Type	iPatch® enabled

Dimensions

Height	31.75 mm 1.25 in
Width	393.7 mm 15.5 in
Depth	12.7 mm 0.5 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)
----------------------	--

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	ACMA CE UL cUL

Packaging and Weights

Packaging quantity	5
Weight, net	0.113 kg 0.25 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

