

ERA® Wireless Communications Switch Subrack, 2 U -48vdc



This unit does not support CAT6A powered access points.

Product Classification

Product Type	Subrack
Product Brand	ERA®

General Specifications

Mounting	Rack
Rack Type	EIA 19 in
Slots Available, quantity	11

Dimensions

Height	88.5 mm 3.484 in
Width	482 mm 18.976 in
Depth	450 mm 17.717 in

Packaging and Weights

Height, packed	522 mm 20.551 in
Width, packed	585 mm 23.032 in
Depth, packed	185 mm 7.283 in
Included	Fan filter Fan tray
Weight, net	7.6 kg 16.755 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

ROHS

Compliant/Exempted

