760237949 | 3298A-C WH 4/23 R1640



3298A-C Category 7A S/FTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft (500 m) length, reel

Product Classification

Regional Availability EMEA

Portfolio SYSTIMAX®

Product Type Twisted pair cable

Ordering Note Available in Europe, Middle East, and Africa

General Specifications

Product Number 3298A-C

ANSI/TIA Category 7A

Cable Component Type Horizontal

Cable Type S/FTP (shielded)

Conductor Type, singles Solid

Conductors, quantity 8

Jacket Color White

Pairs, quantity 4

Transmission Standards ANSI/TIA-568.2-D | CENELEC EN 50288-9-1 | IEC 61156-5 Cat

7 | ISO/IEC 11801 Class FA

Dimensions

Cable Length 500 m | 1,640.42 ft

Cable Length Tolerance ±5%

 Diameter Over Jacket, nominal
 7.493 mm | 0.295 in


 Jacket Thickness
 0.635 mm | 0.025 in

Conductor Gauge, singles 23 AWG

Cross Section Drawing



760237949 | 3298A-C WH 4/23 R1640



Electrical Specifications

dc Resistance Unbalance, maximum 2 %

dc Resistance, maximum 7.61 ohms/100 m | 2.32 ohms/100 ft

Mutual Capacitance at Frequency 4.3 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 76 %

Operating Frequency, maximum 1000 MHz

Operating Voltage, maximum 80 V

Material Specifications

Conductor MaterialBare copperInsulation MaterialPolyolefin

Jacket Material Low Smoke Zero Halogen (LSZH)

Shield (Braid) Material Tinned copper

Shield (Tape) Material Polyester/Aluminum shield

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature $0 \,^{\circ}\text{C}$ to +50 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +122 $^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Acid Gas Test Method EN 50267-2-3

COMMSCOPE®

760237949 | 3298A-C WH 4/23 R1640

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Ratings1EN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)

Smoke Test Method IEC 61034-2

Packaging and Weights

Cable weight 64.125 kg/km | 43.09 lb/kft

Packaging Type Reel

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



