

EWP132, HELIAX® Premium Elliptical Waveguide, 14.0–14.5 GHz, black PE jacket

#### **Product Classification**

Product Type Premium elliptical waveguide

Product Brand HELIAX®
Product Series Premium

General Specifications

Jacket Color Black

Performance Note Values typical, unless otherwise stated

**Dimensions** 

Diameter Over Jacket (E Plane)24.4 mm | 0.961 inDiameter Over Jacket (H Plane)15.5 mm | 0.61 in

**Cable Volume** 167 L/km | 1.798 ft³/kft

**Electrical Specifications** 

eTE11 Mode Cutoff 9.22 GHz

**Group Delay at Frequency** 131 ns/100 ft @ 14.700 GHz | 428 ns/100 m @ 14.700 GHz

**Operating Frequency Band** 14.0 – 14.5 GHz

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

**14.0–14.5 GHz** 1.08 28.3

Attenuation

Frequency (GHz) Attenuation (dB/100 m) Attenuation (dB/100 ft) Average Power (kW) Group Velocity %

**14.0** 16.343 4.982 0.826 75.3

**COMMSCOPE®** 

# EWP132-140

14.2	16.174	4.93	0.835	76.1
14.4	16.018	4.882	0.843	76.8

### Material Specifications

Conductor Material Corrugated copper

Jacket Material PE

### Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)130 mm | 5.118 inMinimum Bend Radius, Multiple Bends (H Plane)360 mm | 14.173 inMinimum Bend Radius, Single Bend (E Plane)130 mm | 5.118 inMinimum Bend Radius, Single Bend (H Plane)360 mm | 14.173 inMaximum Twist6.562 °/m | 2 °/ft

# **Environmental Specifications**

Installation temperature $-40 \, ^{\circ}\text{C}$  to  $+60 \, ^{\circ}\text{C}$  ( $-40 \, ^{\circ}\text{F}$  to  $+140 \, ^{\circ}\text{F}$ )Operating Temperature $-55 \, ^{\circ}\text{C}$  to  $+85 \, ^{\circ}\text{C}$  ( $-67 \, ^{\circ}\text{F}$  to  $+185 \, ^{\circ}\text{F}$ )Storage Temperature $-70 \, ^{\circ}\text{C}$  to  $+85 \, ^{\circ}\text{C}$  ( $-94 \, ^{\circ}\text{F}$  to  $+185 \, ^{\circ}\text{F}$ )

Attenuation, Ambient Temperature $75 \,^{\circ}\text{F}$  |  $23.889 \,^{\circ}\text{C}$ Average Power, Ambient Temperature $104 \,^{\circ}\text{F}$  |  $40 \,^{\circ}\text{C}$ Average Power, Temperature Rise $42 \,^{\circ}\text{C}$  |  $107.6 \,^{\circ}\text{F}$ 

Packaging and Weights

**Cable weight** 0.33 kg/m | 0.222 lb/ft

# Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



