RCT7-C-2A-RNA

RCT7, RADIAX® Coaxial Radiating Cable with Bump, 800–960 MHz, tuned foil, 1-5/8 in, black non-halogenated, fire retardant polyolefin jacket

Product Classification

Product Type Radiating cable

Product Brand RADIAX®
Product Series RCT7

General Specifications

Polarization Vertical

 Cable Type
 Radiating Mode (RCT) Series

Jacket Color Black

Dimensions

 Diameter Over Jacket, maximum
 49.784 mm | 1.96 in

 Inner Conductor OD
 18.161 mm | 0.715 in

 Outer Conductor OD
 43.815 mm | 1.725 in

Nominal Size 1-5/8 in

Recommended Distance from the Wall 101.6 mm | 4 in Recommended Hanger Spacing 1.3 m | 4.265 ft

Electrical Specifications

Attenuation Test Method IEC 61196-4

Attenuation Tolerance ±5%

Cable Impedance50 ohm ±2 ohm

dc Resistance, Inner Conductor1.435 ohms/km| 0.437 ohms/kftdc Resistance, Outer Conductor1.969 ohms/km| 0.6 ohms/kft

dc Test Voltage 15000 V



RCT7-C-2A-RNA

Insulation Resistance 100000 M0hms-km

Jacket Spark Test Voltage (rms) 10000 V

Operating Frequency Band50 - 1000 MHzOptimum Operating Frequency Band800 - 960 MHz

Peak Power 302 kW

Stop Bands 715 – 770 MHz

Velocity 93 %
VSWR Installed, typical, 50–960 MHz 1.3
VSWR on Reel, typical 1.43

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Coupling Loss 50%	Coupling Loss 95%
75.0	0.5	0.15	73	85
100.0	0.6	0.18	70	79
150.0	0.7	0.21	76	89
350.0	1.2	0.37	85	97
450.0	1.4	0.43	75	82
600.0	1.6	0.49	68	71
700.0	1.7	0.52	64	66
800.0	2	0.61	63	65
850.0	2.2	0.67	61	63
900.0	2.4	0.73	59	61
960.0	2.7	0.81	57	60

Material Specifications

Dielectric Material Foam PE

Jacket Material Non-halogenated, fire retardant polyolefin

Inner Conductor Material Corrugated copper tube

Outer Conductor Material Copper foil

Mechanical Specifications

Minimum Bend Radius, single Bend508 mm | 20 inTensile Strength215 kg | 473.993 lbBending Moment16 N-m | 141.612 in lb

Coupling Loss Test Method IEC 61196-4

COMMSCOPE°

RCT7-C-2A-RNA

Coupling Loss Tolerance ±5 dB

Flat Plate Crush Strength 0.8 kg/mm | 44.798 lb/in Indication of Slot Alignment Yes-bumps face the wall

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-30 \,^{\circ}\text{C}$ to $+80 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

Storage Temperature $-30 \,^{\circ}\text{C}$ to $+80 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature68 °F | 20 °CAverage Power, Ambient Temperature104 °F | 40 °CAverage Power, Inner Conductor Temperature212 °F | 100 °C

Fire Retardancy Test Method IEC 60332-1-2 | IEC 60332-3C-24

Smoke Index Test Method IEC 61034

Toxicity Index Test Method IEC 60754-1 | IEC 60754-2

Packaging and Weights

Cable weight 0.83 kg/m | 0.558 lb/ft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

