066112-000 | FOSC600-C4B-NT-0-C4V



FOSC® 600 C Fiber Optic Splice Closure, Gel Cable sealing, butt type, no pre-installed trays, standard basket, one 4-port gel block, four ground feedthrough lugs, with test valve

- Single-ended or in-line, gel-sealed closure for splicing feeder and distribution cables
- Excellent consolidation or rehabilitation closure with large fiber splicing capacity
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability	Latin America North America
Product Type	In-line, rectangular fiber closure Single-ended, rectangular fiber closure
Product Brand	FOSC®
Product Series	FOSC 600
General Specifications	
Cable Entry Drop Port Style	Gel block
Cable Entry Main Port Style	Gel block
Cable Ports Quantity, total	4 multi-out ports (16 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Captured bolts Over-centered latches with rubber gasket
Closure Style	In-line Single-ended
Color	Black
Fiber Storage Basket Type	C6 standard size
Flash Test Valve	Pre-installed
Ground Feed-through	Included
Mounting	Pole Strand Wall
Network Area Type	Feeder Trunk
Splice Tray Included, quantity	0
Splice Tray Type Included	No trays
Splicing Capacity, Mass Fusion, maximum	864

Page 1 of 3


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



066112-000 | FOSC600-C4B-NT-0-C4V

Splicing Capacity, Single Fusion, maximum	480
Splicing Capacity, Single Splice, 12 fibers, maximum	480
Splicing Capacity, Single Splice, 6 fibers, maximum	180
Splicing Type, Supported	Mass fusion Single fusion
Dimensions	
Height	152 mm 5.984 in
Width	274 mm 10.787 in
Length	828 mm 32.598 in
Main Cable Diameter, maximum	35 mm 1.378 in

Ordering Tree



Material Specifications

Material Type

Environmental Specifications

Environmental Space

Rugged polymer

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



066112-000 | FOSC600-C4B-NT-0-C4V

Qualification Standards

Water Resistance

Packaging and Weights

Packaging quantity	
Packaging Type	
Weight, net	

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Telcordia GR-771-CORE, 20 ft waterhead Flash test valve at 5 psi (40 kPa)

1 Box | Carton 11.79 kg | 25.992 lb

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024

