

# CAAAD | IP6A-12PUTP-01S-01S

## Base Product



InstaPATCH® Cu GigaSPEED X10D® U/UTP Plenum Preterminated Copper Cable, single row standard density outlet to single row standard density outlet, 12 links

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Copper trunk cable assembly   |
| <b>Product Brand</b>         | GigaSPEED X10D®   InstaPATCH® Cu                                    |

## General Specifications

|                                       |                               |
|---------------------------------------|-------------------------------|
| <b>ANSI/TIA Category</b>              | 6A                            |
| <b>Cable Type</b>                     | U/UTP (unshielded)            |
| <b>Conductor Type</b>                 | Solid                         |
| <b>Interface, Connector A</b>         | Information outlet            |
| <b>Interface Feature, connector A</b> | Single row   Standard density |
| <b>Interface, Connector B</b>         | Information outlet            |
| <b>Interface Feature, connector B</b> | Single row   Standard density |
| <b>Link Count</b>                     | 12                            |
| <b>Wiring</b>                         | T568B                         |

## Dimensions

|   |          |
|---|----------|
| <b>Cable Assembly Length Range (m)</b>  | 5 – 90   |
| <b>Cable Assembly Length Range (ft)</b> | 17 – 295 |

## Electrical Specifications

|                               |         |
|-------------------------------|---------|
| <b>dc Resistance, maximum</b> | 0.3 ohm |
| <b>Safety Voltage Rating</b>  | 300 V   |

## Ordering Tree



# 2091B-4/23

---



GigaSPEED X10D® 2091B ETL Verified Category 6A U/UTP Cable, 4 pair count

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Product Type</b>          | Twisted pair cable  |
| <b>Product Brand</b>         | GigaSPEED X10D®   |


## General Specifications

|                                |  |
|--------------------------------|--|
| <b>Product Number</b>          | 2091B  |
| <b>ANSI/TIA Category</b>       | 6A   |
| <b>Cable Component Type</b>    | Horizontal   |
| <b>Cable Type</b>              | U/UTP (unshielded)   |
| <b>Conductor Type, singles</b> | Solid  |
| <b>Conductors, quantity</b>    | 8  |
| <b>Note</b>                    | Consult ANSI/TIA-568-C.2 Annex G for length de-rating guidance for cable installation in higher temperature environments |
| <b>Pairs, quantity</b>         | 4  |
| <b>Separator Type</b>          | Isolator   |
| <b>Transmission Standards</b>  | ANSI/TIA-568.2-D   ISO/IEC 11801 Class EA  |

## Dimensions

|                                      |                     |
|--------------------------------------|---------------------|
| <b>Diameter Over Jacket, nominal</b> | 7.239 mm   0.285 in |
| <b>Jacket Thickness</b>              | 1.295 mm   0.051 in |
| <b>Conductor Gauge, singles</b>      | 23 AWG              |

## Cross Section Drawing



## Electrical Specifications

|  |   |
|--|---|
| <b>dc Resistance Unbalance, maximum</b>      | 4 %   |
| <b>dc Resistance, maximum</b>                | 7.61 ohms/100 m   2.32 ohms/100 ft  |
| <b>Dielectric Strength, minimum</b>          | 1500 Vac   2500 Vdc   |
| <b>Mutual Capacitance at Frequency</b>       | 6.0 nF/100 m @ 1 kHz  |
| <b>Nominal Velocity of Propagation (NVP)</b> | 66 %  |
| <b>Operating Frequency, maximum</b>          | 550 MHz   |
| <b>Operating Voltage, maximum</b>            | 80 V  |
| <b>Remote Powering</b>                       | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |

## Material Specifications

|                             |             |
|-----------------------------|-------------|
| <b>Conductor Material</b>   | Bare copper |
| <b>Insulation Material</b>  | FEP         |
| <b>Jacket Material</b>      | PVC         |
| <b>Separator Material</b>   | FEP         |
| <b>Separator 2 Material</b> | Polyolefin  |

## Mechanical Specifications

# 2091B-4/23

---

**Pulling Tension, maximum** 11.34 kg | 25 lb

## Environmental Specifications

**Installation temperature** 0 °C to +60 °C (+32 °F to +140 °F)

**Operating Temperature** -20 °C to +75 °C (-4 °F to +167 °F)

**Environmental Space** Plenum

**Temperature Rating, UL** 105 °C | 221 °F

**Flame Test Method** CMP/FT6

**Safety Standard** UL 444

**Smoke Test Method** CMP/FT6 | NFPA 262

## Packaging and Weights

**Cable weight** 60.568 kg/km | 40.7 lb/kft

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

# MGS600

## Base Product



GigaSPEED X10D® M-Series Modular Jack, RJ45, Cat6A Unshielded

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

SYSTIMAX®

### Product Type

Modular jack

### Product Brand

GigaSPEED X10D®

### Product Series

MGS600

## General Specifications

### ANSI/TIA Category

6A

### Cable Type

Unshielded

### Conductor Type

Solid | Stranded

### Termination Type

IDC

### Wiring

T568A | T568B

## Dimensions

### Height

19.4 mm | 0.764 in

### Width

21.08 mm | 0.83 in

### Depth

30.2 mm | 1.189 in

### Compatible Conductor Gauge, solid

22 AWG | 24 AWG

### Compatible Conductor Gauge, stranded

22 AWG | 24 AWG

## Electrical Specifications

### Contact Resistance Variation, maximum

20 mOhm

### Contact Resistance, maximum

100 mOhm

# MGS600

---

|  |  |
|--|--|
| <b>Current Rating at Temperature</b>                         | 1.5 A @ 20 °C   1.5 A @ 68 °F  |
| <b>Dielectric Withstand Voltage, RMS, conductive surface</b> | 1,500 Vac @ 60 Hz  |
| <b>Dielectric Withstand Voltage, RMS, contact-to-contact</b> | 1,000 Vac @ 60 Hz  |
| <b>Insulation Resistance, minimum</b>                        | 500 MOhm   |
| <b>PoE Durability</b>  | Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles |

## Material Specifications

|                                    |  |
|------------------------------------|--|
| <b>Contact Plating Material</b>    | Precious metals  |
| <b>Material Type</b>               | Copper alloy   High-impact, flame retardant, thermoplastic |
| <b>Termination Contact Plating</b> | Nickel   |

## Mechanical Specifications

|                                      |                                |
|--------------------------------------|--------------------------------|
| <b>Plug Retention Force, minimum</b> | 133 N   29.9 lbf               |
| <b>Plug to Jack Mating Cycles</b>    | Complies to IEC 60603-7 series |

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Storage Temperature</b>   | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Relative Humidity</b>     | Up to 95%, non-condensing            |
| <b>Flammability Rating</b>   | UL 94 V-0                            |
| <b>Safety Standard</b>       | UL   cUL                             |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |