# SSC-760236114 | Radio Enclosure Pico for Nokia or Ericsson



### Middle of Pole Pico Concealment Enclosure for Ericsson and Nokia Radios

- Intended to be used with remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

#### SSC-760236114E1x

Up to (6) 2203/2205/2208/440x Radios

Up to (2) 220x/440x and (1) 4435 with separaterly ordered kit "860665179-AMK-002".

#### SSC-760236114E4x

(1) 4415/4426 Radio & (1) 220X/440x & (1) PSU AC 02/08

Or

(1) 8843 and (2) PSU-AC-02/08 with separate kit "860660900-1"

#### SSC-760236114N2x

Up to (4) AirScale Micro Radios

#### SSC-760236114N3x

- (1) Nokia Dual Band 160W Radio & (1) AirScale Micro Radio or 1 AHFIB &
- (1) DC Rectifier (Nokia FPAE OR Delta 1kW or 1.8kW)

### **Product Classification**

Portfolio CommScope®

Product Type Mid pole
Product Brand Metro Cell

Ordering Note CommScope® standard product with terms

**Warranty** One year

## General Specifications

Antennas Included None

**Color** Light Gray (RAL 7035)

Color Options Beige-Grey (RAL 7006) | Black (RAL 9005) | Black Green (RAL 6012) | Brown (RAL

8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Pure White | Umbra

Grey (RAL 7022)

**Cooling** Passive Cooling

Mounting Options Non-tapered poles | Tapered poles | Wood poles

Power Supply Compatibility PSU-AC-08

**COMMSCOPE®** 

# SSC-760236114 | Radio Enclosure Pico for Nokia or Ericsson

**Radio Compatibility, Ericsson** (1) 4415/4426 Radio & (1) 2203/2205/2208 & (1) PSU AC

08 | 220x | 440x | 4435 | 8843 | Power Distribution

Radio Compatibility, Nokia (1) Airscale Dual Band 160W + (1) AirScale micro radio | AHFIA | AHFIB | Power

Distribution | Up to (4) AirScale micro radios

Radios Included None

**Dimensions** 

 Height
 1016 mm | 40 in

 Width
 401.32 mm | 15.8 in

 Depth
 304.8 mm | 12 in

**Electrical Specifications** 

Power/Fiber Input Trade size knockouts at rear side

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

**Environmental Specifications** 

Thermal Compliance GR-487

Packaging and Weights

 Volume
 0.125 m³ | 4.4 ft³

 Weight (loaded)
 36.287 kg | 80 lb

 Weight (unloaded)
 18.144 kg | 40 lb

\* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines

