

Compact Quad WCS IMF for Aeronautical Mobile Telemetry Band Co-Location, 4.3-10

- New 4.3-10 connectors for improved PIM performance and size reduction
- DC/AISG passing capability from BTS port to ANT port
- Convertible mounting brackets
- Small size excellent for metro cell applications

Product Classification

Product Type Interference mitigation filter

General Specifications

Color Gray
Modularity 4-Quad

Mounting Pipe HardwareBand clamps (2)RF Connector Interface4.3-10 Female

Dimensions


 Height
 162 mm | 6.378 in

 Width
 206 mm | 8.11 in

 Depth
 176 mm | 6.929 in

Outline Drawing





Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through PathBranch 1Lightning Surge Current8 kA

Lightning Surge Current Waveform 8/20 waveform

Electrical Specifications

Sub-module	1 2 3 4	1 2 3 4	1 2 3 4	1 2 3 4
Branch	1	1	1	1
Port Designation	Uplink	Downlink	Downlink	Downlink
License Band	WCS 2300, Band Pass			

Electrical Specifications, Band Pass

Frequency Range, MHz	2305-2315	2350-2357	2357-2358.6	2358.6-2358.96
Insertion Loss, maximum, dB	0.7	0.6	1.2	1.8
Insertion Loss, typical, dB	0.5	0.5	0.8	1.3

Page 2 of 4




Total Group Delay, maximum, ns	35	380	550	550
Return Loss, minimum, dB	18	18	18	18
Return Loss, typical, dB	20	20	20	20
Input Power, RMS, maximum, W		100	100	100
Input Power, PEP, maximum, W		1000	1000	1000
Higher Order PIM, minimum, dBc		-160	-160	-160
Higher Order PIM Test Method		2 x 20 W CW tones	2 x 20 W CW tones	2 x 20 W CW tones

Electrical Specifications, Band Reject

Frequency Range, MHz 2360-2395

Attenuation, minimum, dB 43

Block Diagram



Mechanical Specifications

 Wind Loading @ Velocity, frontal
 48.0 N @ 150 km/h (10.8 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 37.0 N @ 150 km/h (8.3 lbf @ 150 km/h)

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Ingress Protection Test Method IEC 60529:2001, IP67

COMMSCOPE®

Packaging and Weights

IncludedMounting hardwareWeight, net8.1 kg | 17.857 lb

