


190SCM



Fixed-tuned PBR100 for elliptical waveguide 90

Product Classification

Product Type Elliptical waveguide connector

General Specifications

Attachment Method Tab-flare | Tool-flare

Body Style Straight, fixed-tuned

Inner Contact Plating Unplated

Interface PBR100

Outer Contact Plating Unplated

Pressurizable Yes

Dimensions

Width 55.88 mm | 2.2 in

Length 80.772 mm | 3.18 in

Transition Length 46.228 mm | 1.82 in

Waveguide Size WR90 | WG16 | R100

Electrical Specifications

Insertion Loss, typical 0.01 dB

Operating Frequency Band 10.2 – 11.7 GHz

Peak Power at Frequency, maximum 44.90 kW @ 11.20 GHz

Material Specifications

Material Type Brass

190SCM

Environmental Specifications

Operating Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Storage Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Packaging and Weights

Weight, net 1 kg | 2.205 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |



* Footnotes

Insertion Loss, typical 0.05√freq (GHz) (not applicable for elliptical waveguide)