

5NF4 Category 5e U/UTP filled Cable, outdoor direct burial, black jacket, 4 pair count, 1000 ft (305 m) length, reel

Product Classification

Regional Availability

Latin America | North America

Portfolio CommScope®

Product Type Twisted pair cable

General Specifications

Product Number 5NF4
ANSI/TIA Category 5e

Cable Component Type Horizontal

Cable Type U/UTP (unshielded)

 Conductor Type, singles
 Solid

 Conductors, quantity
 8

 Jacket Color
 Black

Note All electrical transmission tests include swept frequency measurements

Pairs, quantity 4

Transmission Standards ANSI/TIA-568.2-D | CENELEC EN 50288-3-1 | ISO/IEC 11801 Class D

Dimensions

 Cable Length
 304.8 m | 1000 ft


 Diameter Over Jacket, nominal
 6.096 mm | 0.24 in

 Jacket Thickness
 0.762 mm | 0.03 in

Conductor Gauge, singles 24 AWG

Cross Section Drawing





Electrical Specifications

Characteristic Impedance 100 ohm

dc Resistance Unbalance, maximum $5\,\%$

dc Resistance, maximum 9.38 ohms/100 m | 2.859 ohms/100 ft

Delay Skew, maximum 45 ns

Dielectric Strength, minimum 1500 Vac | 2500 Vdc

Mutual Capacitance at Frequency 4.6 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 65 %

Operating Frequency, maximum 350 MHz

Operating Voltage, maximum 80 V

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the

safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Safety Voltage Rating 300 V

Flectrical Cable Performance

CS CommScope

STD Refers to the standard value listed under Transmission Standards in the Electrical Specifications above

TYP Typical Electrical Performance

IL Insertion Loss (dB/100m) NEXT Near End Crosstalk (dB/100m)

 ACR
 Attenuation to Crosstalk Ratio (dB/100m)
 PSNEXT
 Power Sum Near End Crosstalk (db/100m)

 PSACR
 Power Sum Attenuation to Crosstalk Ratio (dB/100m)
 ACRF
 Attenuation to Crosstalk Ratio - Far End (dB/100m)

PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m) RL Return Loss (dB)

TCL Transverse Conversion Loss (dB/100m) ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL			NEXT			ACR			PSNEXT			PSACR			ACRF			PSACRF			RL		
	CS	STD	TYP	cs	STD	TYP	cs	STD	TYP	cs	STD	TYP	cs	STD	TYP	cs	STD	TYP	cs	STD	TYP	cs	STD	TYP
1	2	2	1.8	70.3	65.3	87.9	68.3	63.3	86.1	68.3	62.3	86	66.3	60.3	84.2	67.8	63.8	81	65	60.8	79.8	20	20	31.5
4	3.9	4.1	3.5	61.3	56.3	79	57.3	52.2	75.5	59.3	53.3	77	55.3	49.2	73.4	55.8	51.8	69	53.8	48.8	67.9	23.3	23	29.8
8	5.6	5.8	5	56.8	51.8	74	51.2	46	69	54.8	48.8	72	49.2	43	67	49.7	45.7	62.8	47.7	42.7	61.7	25	24.5	32.8
10	6.2	6.5	5.6	55.3	50.3	72.5	49.1	43.8	66.9	53.3	47.3	70.7	47.1	40.8	65.1	47.8	43.8	60.9	45.8	40.8	59.8	25.5	25	34.3
16	7.9	8.2	7.1	52.2	47.2	69.8	44.3	39	62.8	50.2	44.2	67.7	42.3	36	60.6	43.7	39.7	56.8	41.7	36.7	55.7	25.5	25	37.4
20	8.9	9.3	7.9	50.8	45.8	68.4	41.9	36.5	60.5	48.8	42.8	66.2	39.9	33.5	58.3	41.8	37.8	54.9	39.8	34.8	53.7	25.5	25	38.1
25	10	10.4	8.9	49.3	44.3	67.4	39.3	33.9	58.5	47.3	41.3	65.3	37.3	30.9	56.4	39.8	35.8	52.9	37.8	32.8	51.7	24.8	24.3	37.2
31.25	11.3	11.7	9.9	47.9	42.9	66.2	36.6	31.2	56.3	45.9	39.9	64.2	34.6	28.2	54.2	37.9	33.9	50.9	35.9	30.9	49.7	24.1	23.6	34.4
62.5	16.3	17	14.2	43.4	38.4	62.3	27.1	21.4	48.1	41.4	35.4	60.2	25.1	18.4	46	31.9	27.9	44.5	29.9	24.9	43.3	22	21.5	30.7
100	21	22	18.1	40.3	35.3	59.6	19.3	13.3	41.5	38.3	32.3	57.3	17.3	10.3	39.1	27.8	23.8	39.8	25.8	20.8	38.7	20.6	20.1	27.7
155	26.8		22.8	37.4		55.8	10.7		33	35.4		53.9	8.7		31.1	24		36.2	22		34.8	19.3		24.8
200	30.9		26.1	35.8		54.7	4.9		28.6	33.8		52.3	2.9		26.2	21.8		33.5	19.8		32.3	18.5		24
250	35		29.3	34.3		53.1	-0.7		23.7	32.3		50.9	-2.7		21.6	19.8		31.8	17.8		30.5	17.8		23.5
300	38.9		32.2	33.1		50.4	-5.8		18.1	31.1		48.3	-7.8		16.1	18.3		30.5	16.3		29.2	17.3		23.8
350	42.6		35	32.1		48.7	-10.4		13.6	30.1		46.7	-12.4		11.7	16.9		28.6	14.9		27.2	16.8		24.8

Material Specifications

Conductor MaterialBare copperInsulation MaterialPolyolefin

Jacket Material PE

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 °F to +158 °F)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Environmental NoteUV resistant for outdoor and/or direct burial installations

Environmental Space Buried

Page 3 of 4



Packaging and Weights

Cable weight 41.118 kg/km | 27.63 lb/kft

Packaging Type Reel

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

