

7-16 DIN Female High Power Termination Load, 70–2700 MHz

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Termination Load

General Specifications

Device Type

Termination Load

Color

Silver

Interface

7-16 DIN Female

Electrical Specifications

Return Loss, minimum

20 dB

Average Power, maximum

175 W

Impedance

50 ohm

Operating Frequency Band

70 – 2700 MHz


Peak Power, maximum

2 kW

VSWR

1.22

Derating Curve



Environmental Specifications

Operating Temperature	-33 °C to +65 °C (-27.4 °F to +149 °F)
Ingress Protection Test Method	IEC 60529:2001, IP30

Packaging and Weights

Height, packed	242 mm 9.528 in
Width, packed	165 mm 6.496 in
Length, packed	130 mm 5.118 in
Weight, gross	3.7 kg 8.157 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

