

L5CLICKB

Double Click-on Hanger for 7/8 in coaxial cable



Product Classification

Product Type	Hanger kit
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Click-on hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	3
Height	51.1 mm 2.012 in
Width	56.9 mm 2.24 in
Length	111 mm 4.37 in
Compatible Cable Diameter Range	27.7–28.2 mm
Compatible Diameter, maximum	28.2 mm 1.11 in
Compatible Diameter, minimum	27.5 mm 1.083 in
Nominal Size	7/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

L5CLICKB

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 24.4 cm | 9.606 in

Width, packed 13.4 cm | 5.276 in

Length, packed 11.5 cm | 4.528 in

Packaging quantity 10

Weight, gross 0.98 kg | 2.161 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power