

CB-LH-25



Locking Heads for Cable Banding CB-12-50, 25 pcs (uses CB-IT installation tool - not incl)

Product Classification

Product Type	Banding
Ordering Note	CommScope® standard product (Global)

General Specifications

Adapter Type	Adapter
Color	Black
Mounting	Round member

Dimensions

Height	12.446 mm 0.49 in
Width	19.05 mm 0.75 in
Length	0.021 m 0.07 ft

Material Specifications

Material Type	Heat-stabilized weather resistant acetal
----------------------	--

Environmental Specifications

Operating Temperature	-65 °C to +90 °C (-85 °F to +194 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	25
---------------------------	----

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
CSA	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

CB-LH-25

ROHS

Compliant

UK-ROHS

Compliant

