



MJC Copper Closure, unpressurized, gel sealed, in-line, for up to 200 pair splices

- Watertight splice closure for aerial, underground and direct buried splices in the unpressurized copper telecommunication network
- Flexible branching plug system allowing installation of cables from 5-pair to 100pair
- Reduced inventory as fewer size closures needed to cover a wide range of applications up to 100 pairs

Product Classification

| | |
|------------------------------|--------------------|
| Regional Availability | EMEA |
| Product Type | Gel sealed closure |
| Product Series | MJC |

General Specifications

| | |
|-----------------------------------|----------------------------------|
| Application | For use with Polyethylene cables |
| Cable Capacity, maximum | 8 |
| Cable Sealing Type | Gel filled |
| Closure Style | In-line |
| Color | Black |
| Splicing Capacity, maximum | 200 |

Dimensions

| | |
|--|-------------------|
| Single Cable Diameter, maximum | 28 mm 1.102 in |
| Single Cable Diameter, minimum | 7 mm 0.276 in |
| Splice Bundle Diameter, maximum | 120 mm 4.724 in |

Environmental Specifications

| | |
|----------------------------|-----------------|
| Environmental Space | Aerial Buried |
|----------------------------|-----------------|

Packaging and Weights

| | |
|---------------------------|--------------|
| Packaging quantity | 1 |
| Packaging Type | Bag Carton |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

