



Fiber Optic Pigtail, 12 fibers, Singlemode, LSH/APC to Stub, 0.9 mm diameter, multicolor, 2 m

## Product Classification

|                              |                            |
|------------------------------|----------------------------|
| <b>Regional Availability</b> | EMEA                       |
| <b>Product Type</b>          | Fiber pigtail, multi-fiber |
| <b>Product Series</b>        | OCP                        |

## General Specifications

|                               |         |
|-------------------------------|---------|
| <b>Connector A, quantity</b>  | 12      |
| <b>Color, boot A</b>          | Green   |
| <b>Color, connector A</b>     | Green   |
| <b>Interface, Connector A</b> | LSH/APC |
| <b>Total Fibers, quantity</b> | 12      |

## Dimensions

|                             |                   |
|-----------------------------|-------------------|
| <b>Cord Length</b>          | 2 m   6.562 ft    |
| <b>Diameter Over Jacket</b> | 0.9 mm   0.035 in |

## Ordering Tree

# 760246010 | OCP-EC-02MASEN-XX-(12COL)



| Connector/adapter type |                  |            |
|------------------------|------------------|------------|
| Standard C grade       | Superior B grade | Type       |
| S1                     | SF               | SC/UPC     |
| S2                     | SG               | SC/APC 8°  |
| S3                     | SH               | SC/APC 9°  |
| L1                     | LF               | LC/UPC     |
| L2                     | LG               | LC/APC     |
| -                      | EC               | LSH/APC 8° |

| Cable type |        |                   | Fiber type |
|------------|--------|-------------------|------------|
| ASEN       | 900 μm | Semi-tight jacket | A1         |
| HSEN       | 900 μm | Semi-tight jacket | A2         |

| Cable length |          |
|--------------|----------|
| 02           | 2 meters |

- Standard Configuration by default 900μm buffer  
 buffer color : yellow  
 250 μm color : natural or milky white

## Optical Specifications

|   |                      |
|---|----------------------|
| <b>Fiber Mode</b>                           | Singlemode           |
| <b>Fiber Type</b>                           | G.657.A1, TeraSPEED® |
| <b>Insertion Loss, maximum, connector A</b> | 0.25 dB              |
| <b>Return Loss, minimum, connector A</b>    | 60 dB                |

## Environmental Specifications

|                            |                               |
|----------------------------|-------------------------------|
| <b>Environmental Space</b> | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

