


1711910-1



Copper Cable, category 7A, 4 pair simplex, S/FTP, LSFRZH, 23 AWG solid, 1000 m, white

Product Classification

Regional Availability	Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair cable

General Specifications

ANSI/TIA Category	7A
Cable Component Type	Horizontal
Cable Type	S/FTP (shielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	White
Pairs, quantity	4
Transmission Standards	CENELEC EN 50288-9-1 EN 50173-1 IEC 61156-5 Cat 7 ISO/IEC 11801 Class FA

Dimensions

Cable Length	1,000 m 3,280.84 ft
Diameter Over Insulated Conductor	1.45 mm 0.057 in
Diameter Over Jacket, nominal	7.493 mm 0.295 in
Conductor Gauge, singles	23 AWG

Electrical Specifications

Coupling Attenuation	Type I
Operating Frequency, maximum	1000 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA

Segregation Class

d

Electrical Cable Performance

CS	CommScope	NEXT	Near End Crosstalk (dB/100m)
STD	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	PSNEXT	Power Sum Near End Crosstalk (db/100m)
TYP	Typical Electrical Performance	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
IL	Insertion Loss (dB/100m)	RL	Return Loss (dB)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
TCL	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL		NEXT		PSNEXT		PSACRF		RL	
	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	
1	2	78	97	75	92	75	90	20	26	
10	5	78	97	75	92	72.3	90	25	35	
100	17	75	97	73	92	52.3	86	20	40	
200	24	71	97	68	91	46.3	79	18	36	
250	27	69	97	66	91	44.3	76	17.3	34	
500	38	65	97	62	91	38.3	64	17.3	29	
600	42	64	95	61	90	36.7	57	17.3	25	
700	47	63	93	60	88	35.4	54	16.6	25	
800	51	62	91	59	86	34.2	50	16.1	24	
900	55	61	90	58	85	33.2	46	15.5	23	
1,000	58	60	88	57	83	32.3	41	15.1	21	
1,100	59		87		82		32		21	
1,200	62		86		81		28		20	
1,300	65		86		81		25		20	

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	Low Smoke Fire Retardant Zero Halogen (LSFRZH)
Shield (Tape) Material	Aluminum/Polyester

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s2
EN50575 CPR Cable EuroClass Droplets Rating	d1

EN50575 CPR Cable EuroClass Acidity Rating a1

Packaging and Weights

Packaging Type Reel

Regulatory Compliance/Certifications

Agency

Classification

CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

