

MC-CP12M-B-J

3-Sector Adjustable Monopole Co-location Platform Base Kit, 15 in to 50 in OD, 12 ft 6 in face, No antenna pipes included.



Product Classification

Product Type Co-location platform

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 0

Sectors, quantity 3

Dimensions

Face Width 3.81 m | 12.5 ft

Width 3,810 mm | 150 in

Face Support Pipe Diameter 73.152 mm | 2.88 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Platform | Rail | Ring mount

Packaging quantity 1

Weight, net 578.92 kg | 1,276.3 lb