222040-2

EWP90S, HELIAX® Super Premium Elliptical Waveguide, 10.7–11.7 GHz, unjacketed

Product Classification

Product Type Super premium elliptical waveguide

HELIAX® Product Brand

Product Series Super Premium

General Specifications

Performance Note Values typical, unless otherwise stated

Dimensions

Diameter Over Jacket (E Plane) 33.5 mm | 1.319 in **Diameter Over Jacket (H Plane)** 20.3 mm | 0.799 in

Cable Volume 334 L/km | 3.595 ft3/kft

Electrical Specifications

eTE11 Mode Cutoff 6.5 GHz

125 ns/100 ft @ 11.200 GHz | 410 ns/100 m @ 11.200 GHz **Group Delay at Frequency**

Operating Frequency Band 10.7 - 11.7 GHz

VSWR/Return Loss

VSWR Frequency Band Return Loss (dB) 1.05

Attenuation

10.7-11.7 GHz

Frequency (GHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)	Group Velocity %
10.7	10.311	3.143	1.559	79.4
10.9	10.198	3.108	1.576	80.3
11.1	10.096	3.077	1.592	81.1
11.3	10.004	3.049	1.606	81.8
11.5	9.92	3.024	1.62	82.5
11.7	9.843	3	1.633	83.1

32.3

Material Specifications



222040-2

Conductor Material Corrugated copper

Jacket Material Unjacketed

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)180 mm | 7.087 inMinimum Bend Radius, Multiple Bends (H Plane)480 mm | 18.898 inMinimum Bend Radius, Single Bend (E Plane)150 mm | 5.906 inMinimum Bend Radius, Single Bend (H Plane)330 mm | 12.992 inMaximum Twist6.562 °/m | 2 °/ft

Environmental Specifications

Installation temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-55 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-67 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Storage Temperature $-70 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-94 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Attenuation, Ambient Temperature 75 °F | 23.889 °C

Average Power, Ambient Temperature $$104\ ^{\circ}\text{F}\ |\ 40\ ^{\circ}\text{C}$$

Average Power, Temperature Rise 42 °C | 107.6 °F

Packaging and Weights

Cable weight 0.48 kg/m | 0.323 lb/ft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

