EW43, HELIAX® Standard Elliptical Waveguide, 4.4–5.0 GHz, black PE jacket

Product Classification

Product Type Product Brand		Standard elliptical waveguide HELIAX®		
Product Brand		Standard		
General Specifications				
Jacket Color		Black		
Performance Note		Values typical, unless otherwise stated		
Dimensions				
Diameter Over Jacket (E Plane)		71 mm 2.795 in		
Diameter Over Jacket (H Plane)		41 mm 1.614 in		
Cable Volume		1690 L/km 18.191 ft ³ /kft		
Electrical Specifications				
eTE11 Mode Cutoff		2.78 GHz		
Group Delay at Frequency		128 ns/100 ft @ 4.600 GHz 419 ns/100 m @ 4.600 GHz		
Operating Frequency Band		4.4 – 5.0 GHz		
VSWR/Return Loss				
Frequency Band	VSWR	Return Loss (dB)		
4.4–5.0 GHz	1.15	23.13		
Attenuation				
Frequency (GHz)	Attenuation (dB/100 m) Attenuation (dB/100 ft)	Average Power (kW)	Group Velocity %
4.4	2.983	0.909	9.52	77.5

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

COMMSCOPE®

EW43

4.5	2.948	0.899	9.632	78.6
4.6	2.917	0.889	9.734	79.7
4.7	2.889	0.881	9.827	80.6
4.8	2.864	0.873	9.912	81.5
4.9	2.842	0.866	9.99	82.3
5.0	2.822	0.86	10.061	83.1

Material Specifications

Conductor Material	Corrugated copper
Jacket Material	PE

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	381 mm 15 in
Minimum Bend Radius, Multiple Bends (H Plane)	1016 mm 40 in
Minimum Bend Radius, Single Bend (E Plane)	280 mm 11.024 in
Minimum Bend Radius, Single Bend (H Plane)	711 mm 27.992 in
Maximum Twist	1.64 °/m 0.5 °/ft

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)
Attenuation, Ambient Temperature	75°F 23.889°C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Temperature Rise	42 °C 107.6 °F

Packaging and Weights

Cable weight

1.2 kg/m | 0.806 lb/ft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023







Compliant



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

