A-100329

Base Product



Link ac Cabinet, Mark 4

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type Power supply enclosure

Ordering Note For UK region only

General Specifications

Access Front door

Batteries Supported 0

Cabinet Type Integrated cabinet

Color Green | Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

Cooling 175 mm fan (1)

Door Security European profile cylinder

Doors, quantity 2

Mounting Plinth | Root

Rack Type EIA 19 in

Rack Units 13

Dimensions

 Height
 1524 mm | 60 in

 Width
 609.6 mm | 24 in

 Depth
 508 mm | 20 in

Electrical Specifications

Input Power Supply 100 A

ac Distribution Type 20-way plastic enclosure

dc Distribution Type8-way dc panel | Power supply unit

Generator Connection No connection

Power Phase Single

COMMSCOPE®

A-100329

Rectifier Power 800 W

Rectifiers, quantity 2

Voltage 230 Vac

Material Specifications

Finish Powder coated

Material Type Galvanized steel

Environmental Specifications

Qualification Standards IEC 60529: 2001 | IEE Wiring Regulations BS 7671 | IP55

Packaging and Weights

Included -48V DC Power supply unit | Brackets | Cooling | Installation Kit | Power Distribution

Weight, net 150.139 kg | 331 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

