

12-port sector antenna, 2x 698-803, 2x 824-894 and 8x 1695-2360 MHz, 65° HPBW, 4x RETs and low bands have diplexers.

- Internal filter on low band and interleaved dipole technology providing for attractive, low wind load mechanical package
- One RET for 700MHz, one RET for 850MHz, and one RET for each side-by-side pair of high bands to ensure same tilt level for 4x Rx or 4x MIMO

General Specifications

Antenna Type Sector

Band Multiband

Color Light Gray (RAL 7035)

Grounding TypeRF connector body grounded to reflector and mounting bracket

Performance Note

Outdoor usage | Wind loading figures are validated by wind tunnel

measurements described in white paper WP-112534-EN

Radome MaterialFiberglass, UV resistantRadiator MaterialLow loss circuit board

Reflector Material Aluminum

RF Connector Interface 4.3-10 Female

RF Connector LocationBottom

RF Connector Quantity, high band 8
RF Connector Quantity, low band 4
RF Connector Quantity, total 12

Remote Electrical Tilt (RET) Information

RET Hardware CommRET v2

RET Interface 8-pin DIN Female | 8-pin DIN Male

RET Interface, quantity 1 female | 1 male

Input Voltage 10-30 Vdc

Internal RET High band (2) | Low band (2)

Power Consumption, active state, maximum8 WPower Consumption, idle state, maximum1 WPower Consumption, normal conditions, maximum8 W

Page 1 of 7

Protocol 3GPP/AISG 2.0 (Multi-RET)

Dimensions


Width 350 mm | 13.78 in

Depth 208 mm | 8.189 in

Length 1828 mm | 71.969 in

Net Weight, antenna only 32.7 kg | 72.091 lb


Array Layout



Array ID	Frequency (MHz)	RF Connector	HPBW	RET (MRET)	AISG No.	AISG RET UID	
R1	698-803	1 - 2	65°	1	AISG1	CPxxxxxxxxxxxXMM.1	
R2	824-894	3 - 4	65°	2	AISG1	CPxxxxxxxxxxxXMM.2	
Y2	1695-2360	7 - 8	65°	n	415.64	AISG1	CPxxxxxxxxxxxMM.3
Y4	1695-2360	11 - 12	65°	3	AISGT	CPXXXXXXXXXXXXIVIVI.3	
Y1	1695-2360	5 - 6	65°	4	AICC1	CD: annual annual AMA	
Y3	1695-2360	9 - 10	65°		AISG1	CPxxxxxxxxxxxMM.4	

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1695 – 2360 MHz | 698 – 803 MHz | 824 – 894 MHz

Polarization ±45°

Total Input Power, maximum 900 W

Electrical Specifications

	R1	R2	Y1-Y2	Y1-Y2	Y1-Y2	Y1-Y2
Frequency Band, MHz	698-803	824-894	1695-1880	1850-1990	1920-2180	2300-2360
RF Port	1-2	3-4	5-12	5-12	5-12	5-12
Gain, dBi	14.9	15.4	15.8	16.1	16.3	16.8
Beamwidth, Horizontal, degrees	68	66	63	61	63	68
Beamwidth, Vertical, degrees	11.8	10.4	11	10.3	9.7	8.9
Beam Tilt, degrees	2-14	2-14	2-14	2-14	2-14	2-14
USLS (First Lobe), dB	20	19	18	18	19	19
Front-to-Back Ratio at 180°, dB	32	34	35	39	35	38
Isolation, Cross Polarization, dB	25	25	25	25	25	25

Page 3 of 7

Isolation, Inter-band, dB	30	30	30	30	30	30
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	300	300	250	250	250	200

Electrical Specifications, BASTA

Frequency Band, MHz	698-803	824-894	1695-1880	1850-1990	1920-2180	2300-2360
Gain by all Beam Tilts, average, dBi	14.5	15	15	15.6	15.8	16.2
Gain by all Beam Tilts Tolerance, dB	±0.3	±0.3	±0.7	±0.3	±0.3	±0.4
Beamwidth, Horizontal Tolerance, degrees	±2	±1	±4	±2	±2	±4
Beamwidth, Vertical Tolerance, degrees	±0.8	±0.4	±0.6	±0.6	±0.6	±0.3
USLS, beampeak to 20° above beampeak, dB	20	18	18	18	18	16
Front-to-Back Total Power at 180° ± 30°, dB	25	23	27	29	26	28
CPR at Boresight, dB	18	17	18	20	18	19
CPR at Sector, dB	10	11	11	9	11	10

Mechanical Specifications

BASTA Version, mechanical

Wind Loading @ Velocity, frontal

301.0 N @ 150 km/h (67.7 lbf @ 150 km/h)

Wind Loading @ Velocity, lateral

254.0 N @ 150 km/h (57.1 lbf @ 150 km/h)

Wind Loading @ Velocity, maximum 638.0 N @ 150 km/h (143.4 lbf @ 150 km/h)

 $\textbf{Wind Loading @ Velocity, rear} \hspace{1.5cm} 319.0 \text{ N} \textcircled{a} \hspace{0.1cm} 150 \hspace{0.1cm} \text{km/h} \hspace{0.1cm} (71.7 \hspace{0.1cm} \text{lbf} \hspace{0.1cm} \textcircled{a} \hspace{0.1cm} 150 \hspace{0.1cm} \text{km/h})$

Wind Speed, maximum 241.4 km/h (150 mph)

Packaging and Weights

 Width, packed
 456 mm | 17.953 in

 Depth, packed
 357 mm | 14.055 in

 Length, packed
 1975 mm | 77.756 in

 Weight, gross
 42.1 kg | 92.815 lb



Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

BSAMNT-2F – Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical

tilt applications.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



BSAMNT-2F



Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

Product Classification

Product Type Fixed tilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net3.8 kg | 8.378 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity

Weight, gross 4 kg | 8.818 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

COMMSCOPE®



