

6-port sector antenna, 2x 694–960 and 4x 1695–2690 MHz, 65° HPBW, 3x RET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Uses the 4.3-10 connector which is 40 percent smaller than the 7-16 DIN connector

This product will be discontinued on: November 30, 2024

Replaced By:

6P-2L4M-B3 RVV-65B-R3

6-port sector antenna, 2x 694-960 and 4x 1695-2690 MHz, 65° HPBW, 3x RET

General Specifications

Antenna Type Sector

Band Multiband

Grounding TypeRF connector inner conductor and body grounded to reflector and mounting

bracket

Performance Note Outdoor usage | Wind loading figures are validated by wind tunnel

measurements described in white paper WP-112534-EN

RF Connector Interface 4.3-10 Female

RF Connector Location Bottom

RF Connector Quantity, mid band 4
RF Connector Quantity, low band 2
RF Connector Quantity, total 6

Remote Electrical Tilt (RET) Information

RET Interface 8-pin DIN Female | 8-pin DIN Male

RET Interface, quantity 1 female | 1 male

Input Voltage 10-30 Vdc

Internal RET Low band (1) | Mid band (2)

Power Consumption, active state, maximum 10 W Power Consumption, idle state, maximum 1 W

Protocol 3GPP/AISG 2.0

COMMSCOPE®

Dimensions

Width 301 mm | 11.85 in

Depth 180 mm | 7.087 in

Length 1850 mm | 72.835 in

Net Weight, antenna only 23 kg | 50.706 lb

Array Layout



| Array ID | Frequency (MHz) | RF Connector | HPBW | RET (SRET) | AISG No. | AISG RET UID |
|----------|--------------------|--------------|------|---------------|----------|--------------------|
| R1 | 694-960 | 1 - 2 | 65° | 1 | AISG1 | CPxxxxxxxxxxxxxxR1 |
| Y1 | 1695-2690 | 3 - 4 | 65° | 2 | AISG1 | CPxxxxxxxxxxxxxY1 |
| Y2 | 1695-2690 | 5 - 6 | 65° | 3 | AISG1 | CPxxxxxxxxxxxxxxY2 |

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1695 – 2690 MHz | 694 – 960 MHz

Polarization ±45°

Total Input Power, maximum 500 W @ 50 °C

Electrical Specifications

| Frequency Band, MHz | 694-790 | 790-890 | 890-960 | 1695-1920 | 1920-2180 | 2300-2500 | 2500-2690 |
|--|------------|------------|------------|------------|------------|------------|------------|
| Gain at Mid Tilt, dBi | 15 | 15.4 | 15.4 | 17.8 | 18.8 | 19.2 | 19.1 |
| Beamwidth, Horizontal, degrees | 71 | 71 | 68 | 63 | 61 | 61 | 62 |
| Beamwidth, Vertical, degrees | 11.7 | 10.5 | 9.9 | 5.6 | 5 | 4.3 | 4.1 |
| Beam Tilt, degrees | 0-13 | 0-13 | 0-13 | 2-12 | 2-12 | 2-12 | 2-12 |
| USLS (First Lobe), dB | 16 | 16 | 16 | 21 | 19 | 20 | 17 |
| Front-to-Back Ratio at 180°, dB | 29 | 34 | 30 | 30 | 33 | 35 | 32 |
| Front-to-Back Total Power at 180° ± 30°, dB | 23 | 24 | 23 | 24 | 26 | 27 | 25 |
| Isolation, Cross Polarization, dB | 28 | 28 | 28 | 28 | 28 | 28 | 28 |
| Isolation, Inter-band, dB | 30 | 30 | 30 | 30 | 30 | 30 | 30 |
| VSWR Return loss, dB | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 |
| PIM, 3rd Order, 2 x 20 W, dBc | -150 | -150 | -150 | -150 | -150 | -150 | -150 |
| Input Power per Port at 50°C, maximum, watts | 300 | 300 | 300 | 250 | 250 | 250 | 250 |

Electrical Specifications, BASTA

| Frequency Band, MHz | 694-790 | 790-890 | 890-960 | 1695-1920 | 1920-2180 | 2300-2500 | 2500-2690 |
|---|---------|---------|---------|-----------|-----------|-----------|-----------|
| Gain by all Beam Tilts, average, dBi | 14.9 | 15.3 | 15.2 | 17.7 | 18.7 | 19.1 | 18.9 |
| Gain by all Beam Tilts Tolerance, dB | ±0.4 | ±0.3 | ±0.5 | ±0.9 | ±0.5 | ±0.4 | ±0.6 |
| Beamwidth, Horizontal Tolerance, degrees | ±1 | ±1 | ±2 | ±4 | ±5 | ±5 | ±4 |
| Beamwidth, Vertical Tolerance, degrees | ±0.7 | ±0.6 | ±0.5 | ±0.4 | ±0.4 | ±0.2 | ±0.2 |
| USLS, beampeak to 20° above beampeak, dB | 16 | 16 | 17 | 14 | 16 | 16 | 14 |

Page 3 of 6



| CPR at Boresight, dB | 23 | 24 | 23 | 17 | 18 | 19 | 21 |
|----------------------|----|----|----|----|----|----|----|
| CPR at Sector, dB | 11 | 14 | 11 | 12 | 8 | 6 | 9 |

Mechanical Specifications

 Wind Loading @ Velocity, frontal
 281.0 N @ 150 km/h (63.2 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 247.0 N @ 150 km/h (55.5 lbf @ 150 km/h)

 Wind Loading @ Velocity, maximum
 618.0 N @ 150 km/h (138.9 lbf @ 150 km/h)

 Wind Loading @ Velocity, rear
 286.0 N @ 150 km/h (64.3 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

 Width, packed
 409 mm | 16.102 in

 Depth, packed
 299 mm | 11.772 in

 Length, packed
 2036 mm | 80.158 in

 Weight, gross
 34 kg | 74.957 lb

Regulatory Compliance/Certifications

Agency Classification

CE Compliant with the relevant CE product directives

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

BSAMNT-3 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance NoteSevere environmental conditions may degrade optimum performance

COMMSCOPE®

BSAMNT-3



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net6.2 kg | 13.669 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Weight, gross 6.4 kg | 14.11 lb

Regulatory Compliance/Certifications

| Agency | | Classification | | | | | | |
|--|---------------|--|--|--|--|--|--|--|
| CE Compliant with the relevant CE product directives | | Compliant with the relevant CE product directives | | | | | | |
| | CHINA-ROHS | Below maximum concentration value | | | | | | |
| | ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system | | | | | | |
| | REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance | | | | | | |
| | ROHS | Compliant | | | | | | |
| | UK-ROHS | Compliant | | | | | | |
| | | | | | | | | |





