# )B411-B



1-port quasi-omni exposed dipole antenna, 450–470 MHz, 360° HPBW, fixed electrical tilt

- Broad response
- Moisture resistant
- Rugged, reliable design

## General Specifications

**Antenna Type** Omni

**Band** Single band

Color Silver

**Grounding Type** RF connector inner conductor and body grounded to reflector and mounting bracket

**Performance Note** Outdoor usage

**Radiator Material** Aluminum **RF Connector Interface** N Male

**RF Connector Location** End of flexible lead

RF Connector Quantity, low band RF Connector Quantity, total 1

Dimensions

Length 2,870.2 mm | 113 in Net Weight, without mounting kit 11.3 kg | 24.912 lb

**Electrical Specifications** 

**Impedance** 50 ohm

**Operating Frequency Band** 450 - 470 MHz

**Polarization** Vertical

## **Electrical Specifications**

Frequency Band, MHz 450-470

Gain, dBi 11.1 Beamwidth, Horizontal, 360 degrees

Beamwidth, Vertical, degrees 14

**COMMSCOPE®** 

# DB411-B

Beam Tilt, degrees 0

VSWR | Return loss, dB 1.5 | 14.0 Input Power per Port, 250

maximum, watts

Mechanical Specifications

**Wind Loading @ Velocity, maximum** 266.9 N @ 100 mph (60.0 lbf @ 100 mph)

Wind Speed, maximum 161 km/h (100 mph)

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

DB365-OS – Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 -

3.5 in (35 - 89 mm) OD round members.

\* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance



# DB365-0S

Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 - 3.5 in (35 - 89 mm) OD round members.

#### **Product Classification**

**Product Type** Pipe mounting kit

General Specifications

ApplicationOutdoorColorSilver

**Dimensions** 

Compatible Diameter, maximum88.9 mm | 3.5 inCompatible Diameter, minimum33 mm | 1.299 inWeight, net3.2 kg | 7.055 lb

Material Specifications

Material Type Galvanized steel

### Packaging and Weights

Included Brackets | Hardware

Packaging quantity 2

**Weight, gross** 3.6 kg | 7.937 lb

### Regulatory Compliance/Certifications

#### Agency Classification

CE Compliant with the relevant CE product directives

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



