

DB809KE-XT



1-port omni antenna, 806–869 MHz, 360° HPBW, fixed electrical tilt

- Omnidirectional antenna
- Rugged, durable design, heavy duty radome for minimum tip deflection
- Invert mountable

General Specifications

Antenna Type	Omni
Band	Single band
Color	Horizon blue
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Radiator Material	Brass
RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, low band	1
RF Connector Quantity, total	1

Dimensions

Length	3708 mm 145.984 in
Net Weight, without mounting kit	12 kg 26.455 lb
Outer Diameter	76 mm 2.992 in

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	806 – 869 MHz
Polarization	Vertical

Electrical Specifications

Frequency Band, MHz	806–869
Gain, dBi	11.1
Beamwidth, Horizontal,	360

DB809KE-XT

degrees

Beamwidth, Vertical, degrees	8
Beam Tilt, degrees	0
VSWR Return loss, dB	1.5 14.0
PIM, 5th Order, 2 x 20 W, dBc	-150
Input Power per Port, maximum, watts	500

Mechanical Specifications

Wind Loading @ Velocity, maximum	364.8 N @ 100 mph (82.0 lbf @ 100 mph)
Wind Speed, maximum	362 km/h (225 mph)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

DB5091-3	– Pipe Mounting Kit for 3.5 in (88.9 mm) OD round members
----------	---

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---

DB5091-3



Pipe Mounting Kit for 3.5 in (88.9 mm) OD round members

Product Classification

Product Type Pipe mounting kit

General Specifications

Application Outdoor

Color Silver

Dimensions

Compatible Diameter, maximum 88.9 mm | 3.5 in

Compatible Diameter, minimum 33 mm | 1.299 in

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware | Pipe

Packaging quantity 2

Weight, gross 13.2 kg | 29.101 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system