

12-port sector antenna, 2x 698-803, 2x 824-894 and 8x 1695-2360 MHz, 65° HPBW, 4x RETs and low bands have diplexers.

- Internal filter on low band and interleaved dipole technology providing for attractive, low wind load mechanical package
- One RET for 700MHz, one RET for 850MHz, and one RET for each side-by-side pair of high bands to ensure same tilt level for 4x Rx or 4x MIMO

#### General Specifications

Antenna Type Sector
Band Multiband

Color Light Gray (RAL 7035)

**Grounding Type**RF connector body grounded to reflector and mounting bracket

Performance Note Outdoor usage | Wind loading figures are validated by wind tunnel

measurements described in white paper WP-112534-EN

Radome MaterialFiberglass, UV resistantRadiator MaterialLow loss circuit board

Reflector Material Aluminum

**RF Connector Interface** 4.3-10 Female

RF Connector Location Bottom

RF Connector Quantity, high band 8
RF Connector Quantity, low band 4
RF Connector Quantity, total 12

#### Remote Electrical Tilt (RET) Information

**RET Hardware** CommRET v2

RET Interface 8-pin DIN Female | 8-pin DIN Male

**RET Interface, quantity** 1 female | 1 male

Input Voltage 10-30 Vdc

Internal RET High band (2) | Low band (2)

Power Consumption, active state, maximum8 WPower Consumption, idle state, maximum1 WPower Consumption, normal conditions, maximum8 W

Page 1 of 5



Protocol 3GPP/AISG 2.0 (Multi-RET)

**Dimensions** 


**Width** 350 mm | 13.78 in

**Depth** 208 mm | 8.189 in

**Length** 1828 mm | 71.969 in

Net Weight, antenna only 32.7 kg | 72.091 lb


#### Array Layout



Array ID	Frequency (MHz)	RF Connector	HPBW	RET (MRET)	AISG No.	AISG RET UID	
R1	698-803	1 - 2	65°	1	AISG1	CPxxxxxxxxxxxMM.1	
R2	824-894	3 - 4	65°	2	AISG1	CPxxxxxxxxxxxMM.2	
Y2	1695-2360	7 - 8	65°	а	AISG1	AICC1	CPxxxxxxxxxxxMM.3
Y4	1695-2360	11 - 12	65°	3		CPXXXXXXXXXXXXIVIIVI.3	
Y1	1695-2360	5 - 6	65°	_	AICC1	CDAMA 4	
Y3	1695-2360	9 - 10	65°	4	AISG1	CPxxxxxxxxxxxMM.4	

(Sizes of colored boxes are not true depictions of array sizes)

### Port Configuration



#### **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 1695 – 2360 MHz | 698 – 803 MHz | 824 – 894 MHz

Polarization ±45°

**Total Input Power, maximum** 900 W

### **Electrical Specifications**

	R1	R2	Y1-Y2	Y1-Y2	Y1-Y2	Y1-Y2
Frequency Band, MHz	698-803	824-894	1695-1880	1850-1990	1920-2180	2300-2360
RF Port	1-2	3-4	5-12	5-12	5-12	5-12
Gain, dBi	14.9	15.4	15.8	16.1	16.3	16.8
Beamwidth, Horizontal, degrees	68	66	63	61	63	68
Beamwidth, Vertical, degrees	11.8	10.4	11	10.3	9.7	8.9
Beam Tilt, degrees	2-14	2-14	2-14	2-14	2-14	2-14
USLS (First Lobe), dB	20	19	18	18	19	19
Front-to-Back Ratio at 180°, dB	32	34	35	39	35	38
Isolation, Cross Polarization, dB	25	25	25	25	25	25

Page 3 of 5

Isolation, Inter-band, dB	30	30	30	30	30	30
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	300	300	250	250	250	200

#### Electrical Specifications, BASTA

Frequency Band, MHz	698-803	824-894	1695-1880	1850-1990	1920-2180	2300-2360
Gain by all Beam Tilts, average, dBi	14.5	15	15	15.6	15.8	16.2
Gain by all Beam Tilts Tolerance, dB	±0.3	±0.3	±0.7	±0.3	±0.3	±0.4
Beamwidth, Horizontal Tolerance, degrees	±2	±1	±4	±2	±2	±4
Beamwidth, Vertical Tolerance, degrees	±0.8	±0.4	±0.6	±0.6	±0.6	±0.3
USLS, beampeak to 20° above beampeak, dB	20	18	18	18	18	16
Front-to-Back Total Power at 180° ± 30°, dB	25	23	27	29	26	28
CPR at Boresight, dB	18	17	18	20	18	19
CPR at Sector, dB	10	11	11	9	11	10

### Mechanical Specifications

BASTA Version, mechanical

Wind Loading @ Velocity, frontal

301.0 N @ 150 km/h (67.7 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 254.0 N @ 150 km/h (57.1 lbf @ 150 km/h)

 Wind Loading @ Velocity, maximum
 638.0 N @ 150 km/h (143.4 lbf @ 150 km/h)

Wind Loading @ Valority room

210.0 N @ 150 km /b /71.7 lbf @ 150 km /b)

 $\textbf{Wind Loading @ Velocity, rear} \hspace{1.5cm} 319.0 \text{ N} \textcircled{a} \hspace{0.1cm} 150 \hspace{0.1cm} \text{km/h} \hspace{0.1cm} (71.7 \hspace{0.1cm} \text{lbf} \hspace{0.1cm} \textcircled{a} \hspace{0.1cm} 150 \hspace{0.1cm} \text{km/h})$ 

Wind Speed, maximum 241.4 km/h (150 mph)

#### Packaging and Weights

 Width, packed
 456 mm | 17.953 in

 Depth, packed
 357 mm | 14.055 in

 Length, packed
 1975 mm | 77.756 in

 Weight, gross
 42.1 kg | 92.815 lb



#### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

BSAMNT-2F – Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical

tilt applications.

#### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance