LLPX210R-V1



4-port sector antenna, 4x 2300–2700 MHz, 33° HPBW, 2x RET with manual override

Excellent upper sidelobe suppression

General Specifications

Antenna Type Sector

Band Single band

Grounding TypeRF connector inner conductor and body grounded to reflector and

mounting bracket

Performance Note Outdoor usage

Radome Material ASA, UV stabilized

Radiator Material Low loss circuit board

Reflector Material Aluminum

RF Connector Interface 7-16 DIN Female

RF Connector Location Bottom

RF Connector Quantity, high band 4
RF Connector Quantity, total 4

Remote Electrical Tilt (RET) Information

RET Interface 8-pin DIN Male

RET Interface, quantity 2 male
Input Voltage 10-30 Vdc

Internal RET High band (2)

Power Consumption, idle state, maximum 2 W
Power Consumption, normal conditions, maximum 13 W

Protocol 3GPP/AISG 2.0 (Single RET)

Dimensions

 Width
 610 mm | 24.016 in

 Depth
 115 mm | 4.528 in

 Length
 1077 mm | 42.402 in



LLPX210R-V1

Net Weight, without mounting kit 14.5 kg | 31.967 lb

Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 2300 – 2700 MHz

Polarization ±45°

Electrical Specifications

Frequency Band, MHz	2300-2500	2500-2700
Gain, dBi	20.1	20.2
Beamwidth, Horizontal, degrees	34	31
Beamwidth, Vertical, degrees	7.3	6.8
Beam Tilt, degrees	0-10	0-10
USLS (First Lobe), dB	22	19
Null Fill, dB	-22	-22
Front-to-Back Ratio at 180°, dB	33	33
Isolation, Cross Polarization, dB	30	30
VSWR Return loss, dB	1.43 15.0	1.43 15.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150
Input Power per Port, maximum, watts	250	250

Electrical Specifications, BASTA

Frequency Band, MHz	2300-2500	2500-2700
Gain by all Beam Tilts, average, dBi	19.9	19.9
Gain by all Beam Tilts Tolerance, dB	±0.3	±0.7
Gain by Beam Tilt, average, dBi	0° 19.9 5° 19.9 10° 19.8	0° 20.2 5° 20.1 10° 19.3
Beamwidth, Horizontal Tolerance, degrees	±2.2	±2.1
Beamwidth, Vertical Tolerance, degrees	±0.3	±0.2
USLS, beampeak to 20° above beampeak, dB	18	18
Front-to-Back Total Power at 180° ± 30°, dB	29	30
CPR at Boresight, dB	18	19

Mechanical Specifications

 Wind Loading @ Velocity, frontal
 862.0 N @ 150 km/h (193.8 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 70.0 N @ 150 km/h (15.7 lbf @ 150 km/h)

COMMSCOPE®

LLPX210R-V1

Wind Loading @ Velocity, rear 889.0 N @ 150 km/h (199.9 lbf @ 150 km/h)

Wind Speed, maximum 200 km/h (124 mph)

Packaging and Weights

 Width, packed
 693 mm | 27.283 in

 Depth, packed
 221 mm | 8.701 in

 Length, packed
 1285 mm | 50.591 in

 Weight, gross
 32 kg | 70.548 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

T-045-GL-E – Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel


antennas. Includes 2 clamp sets.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



T-045-GL-E



Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

Product Classification

Product Type Adjustable tilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Length, maximum1200 mm | 47.244 inCompatible Length, minimum850 mm | 33.465 inCompatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inAntenna-to-Pipe Distance85 mm | 3.346 inBracket-to-Bracket Distance761 mm | 29.961 inWeight, net6 kg | 13.228 lb

Material Specifications

Material Type Galvanized steel

Mechanical Specifications

Mechanical Tilt 0°-10°

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

T-045-GL-E

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

