### LLPX310R-V1



# 4-port sector antenna, 4x 2300–2700 MHz, 65° HPBW, 2x RET with manual override

• Integrated Internal Remote Electrical Tilt (RET), with independent control of electrical tilt with manual override on all arrays

### General Specifications

Antenna Type Sector

**Band** Single band

**Grounding Type** RF connector inner conductor and body grounded to reflector and

mounting bracket

13 kg | 28.66 lb

Performance Note Outdoor usage | Wind loading figures are validated by wind tunnel

measurements described in white paper WP-112534-EN

**Radome Material** Polyester fiberglass pultrusion

**RF Connector Interface** 7-16 DIN Female

**RF Connector Location** Bottom

RF Connector Quantity, high band 4
RF Connector Quantity, total 4

### Remote Electrical Tilt (RET) Information

**RET Interface** 8-pin DIN Male

**RET Interface, quantity** 1 male

Input Voltage 10-30 Vdc

Internal RET High band (2)

 ${\bf Power \ Consumption, \ idle \ state, \ maximum} \qquad \qquad 2 \ {\bf W}$ 

Power Consumption, normal conditions, maximum 13 W

Protocol 3GPP/AISG 2.0 (Single RET)

#### **Dimensions**

Net Weight, without mounting kit

 Width
 300 mm | 11.811 in

 Depth
 115 mm | 4.528 in

 Length
 1077 mm | 42.402 in

Page 1 of 5

# LLPX310R-V1

### Port Configuration



### **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 2300 – 2700 MHz

Polarization ±45°

### **Electrical Specifications**

Frequency Band, MHz	2300-2500	2500-2700
Gain, dBi	17.2	17.8
Beamwidth, Horizontal, degrees	65	63
Beamwidth, Vertical, degrees	7	6.5
Beam Tilt, degrees	0-10	0-10
USLS (First Lobe), dB	18	18
Front-to-Back Ratio at 180°, dB	30	30
Isolation, Cross Polarization, dB	30	30
VSWR   Return loss, dB	1.43   15.0	1.43   15.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150
Input Power per Port, maximum, watts	250	250

Page 2 of 5



# LLPX310R-V1

### Mechanical Specifications

**Wind Loading @ Velocity, maximum** 450.0 N @ 160 km/h (101.2 lbf @ 160 km/h)

Wind Speed, maximum 200 km/h (124 mph)

Packaging and Weights

 Width, packed
 366 mm | 14.409 in

 Depth, packed
 213 mm | 8.386 in

 Length, packed
 1260 mm | 49.606 in

 Weight, gross
 21.5 kg | 47.399 lb

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



#### Included Products

T-045-GL-E – Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel


antennas. Includes 2 clamp sets.

#### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance



## T-045-GL-E



Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

#### **Product Classification**

**Product Type** Adjustable tilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

**Dimensions** 

Compatible Length, maximum1200 mm | 47.244 inCompatible Length, minimum850 mm | 33.465 inCompatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inAntenna-to-Pipe Distance85 mm | 3.346 inBracket-to-Bracket Distance761 mm | 29.961 inWeight, net6 kg | 13.228 lb

Material Specifications

Material Type Galvanized steel

Mechanical Specifications

Mechanical Tilt 0°-10°

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

# T-045-GL-E

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

