


## Base Product



## KJ-Series Modular Jack, RJ45, Cat6 Unshielded

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Modular jack
<b>Product Series</b>	KJ Series

### General Specifications

<b>ANSI/TIA Category</b>	6
<b>Cable Type</b>	Unshielded
<b>Conductor Type</b>	Solid   Stranded
<b>Mounting</b>	Hubbell® faceplates   Leviton® faceplates   Panduit® faceplates
<b>Outlet Type</b>	Keystone
<b>Termination Tool</b>	110 Punchdown tool   SL Termination tool
<b>Termination Type</b>	IDC
<b>Transmission Standards</b>	ANSI/TIA-568-C.2   ISO/IEC 11801 Class E
<b>Wiring</b>	T568A   T568B

### Dimensions

<b>Panel Cutout, recommended</b>	14.79 x 19.31 mm (0.58 x 0.76 in)
<b>Panel Thickness, recommended</b>	1.6 mm   0.063 in
<b>Height</b>	16.13 mm   0.635 in
<b>Width</b>	16.48 mm   0.649 in
<b>Depth</b>	30.48 mm   1.2 in
<b>Compatible Insulated Conductor Diameter, maximum</b>	1.27 mm   0.05 in
<b>Contact Plating Thickness</b>	1.27 µm
<b>Compatible Conductor Gauge, solid</b>	24–22 AWG

# 2291216

---

**Compatible Conductor Gauge, stranded**

26–24 AWG

## Electrical Specifications

**Remote Powering**

Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002

**PoE Durability**

Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles

## Material Specifications

**Contact Base Material**

Beryllium copper

**Contact Plating Material**

Gold

**Material Type**

Polycarbonate

## Mechanical Specifications

**Plug to Jack Mating Cycles**

Complies to IEC 60603-7 series

## Environmental Specifications

**Flammability Rating**

UL 94 V-0