

6-port sector antenna, 2x 694–960 and 4x 1695–2690 MHz, 65° HPBW, 3x RET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Uses the 4.3-10 connector which is 40 percent smaller than the 7-16 DIN connector

General Specifications

Antenna Type Sector

Band Multiband

Grounding Type RF connector inner conductor and body grounded to reflector and

mounting bracket

Performance Note Outdoor usage | Wind loading figures are validated by wind tunnel

measurements described in white paper WP-112534-EN

Radome MaterialFiberglass, UV resistantRadiator MaterialLow loss circuit board

Reflector Material Aluminum

RF Connector Interface 4.3-10 Female

RF Connector Location Bottom

RF Connector Quantity, high band 4
RF Connector Quantity, low band 2
RF Connector Quantity, total 6

Remote Electrical Tilt (RET) Information

RET Interface 8-pin DIN Female | 8-pin DIN Male

RET Interface, quantity 1 female | 1 male

Input Voltage 10-30 Vdc

Internal RET High band (2) | Low band (1)

Power Consumption, idle state, maximum 2 W
Power Consumption, normal conditions, maximum 13 W

Protocol 3GPP/AISG 2.0 (Single RET)

Dimensions

Width 301 mm | 11.85 in

COMMSCOPE®

Depth

Length

Net Weight, without mounting kit


180 mm | 7.087 in

2645 mm | 104.134 in

27.5 kg | 60.627 lb

Array Layout

RVV65B-C3-3XR, RVV65D-C3-3XR



Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID		
RI	694-960	1-2	- 1	ANxxxxxxxxxxxxxxxxxx1		
Yl	1695-2690	3-4	2	ANxxxxxxxxxxxxxxxxxx2		
Y2	1695-2690	5-6	3	ANxxxxxxxxxxxxxxxx		

View from the front of the antenna

(Sizes of colored boxes are not true depictions of array sizes)

Electrical Specifications

Impedance

Operating Frequency Band

Polarization

Total Input Power, maximum

50 ohm

1695 - 2690 MHz | 694 - 960 MHz

±45°

650 W @ 50 °C

Electrical Specifications

Page 2 of 7

Frequency Band, MHz	694-790	790-890	890-960	1695-1920	1920-2200	2300-2500	2500-2690
Gain, dBi	16.3	17	17	18.1	18.9	19.3	19.2
Beamwidth, Horizontal, degrees	71	70	67	62	60	62	65
Beamwidth, Vertical, degrees	8.1	7.4	6.8	5.6	5	4.3	4.1
Beam Tilt, degrees	0-10	0-10	0-10	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	16	22	18	21	20	21	20
Front-to-Back Ratio at 180°, dB	29	33	31	29	34	33	31
Isolation, Cross Polarization, dB	28	28	28	28	28	28	28
Isolation, Inter-band, dB	30	30	30	30	30	30	30
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	300	300	300	250	250	200	200

Electrical Specifications, BASTA

Frequency Band, MHz	694-790	790-890	890-960	1695-1920	1920-2200	2300-2500	2500-2690
Gain by all Beam Tilts, average, dBi	15.9	16.7	16.7	17.6	18.5	18.9	18.7
Gain by all Beam Tilts Tolerance, dB	±0.6	±0.2	±0.3	±0.8	±0.4	±0.4	±0.6
Gain by Beam Tilt, average, dBi	0° 15.8 5° 15.9 10° 15.9	0° 16.7 5° 16.8 10° 16.6	0° 16.9 5° 16.9 10° 16.4	2° 17.4 7° 17.7 12° 17.6	2° 18.4 7° 18.6 12° 18.4	2° 18.7 7° 19.0 12° 18.6	2° 18.5 7° 18.9 12° 18.4
Beamwidth, Horizontal Tolerance, degrees	±2.5	±1.6	±2.3	±4.2	±5	±6.3	±4.5
Beamwidth, Vertical Tolerance, degrees	±0.4	±0.4	±0.3	±0.4	±0.2	±0.2	±0.2
USLS, beampeak to 20° above beampeak, dB	14	15	15	14	15	15	15
Front-to-Back Total Power at 180° ± 30°, dB	23	25	23	25	25	27	26
CPR at Boresight, dB	21	21	21	18	17	18	20
CPR at Sector, dB	12	14	11	12	9	6	8

Mechanical Specifications

 Wind Loading @ Velocity, frontal
 433.0 N @ 150 km/h (97.3 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 367.0 N @ 150 km/h (82.5 lbf @ 150 km/h)

Page 3 of 7



Wind Loading @ Velocity, maximum 834.0 N @ 150 km/h (187.5 lbf @ 150 km/h)

Wind Loading @ Velocity, rear 439.0 N @ 150 km/h (98.7 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

 Width, packed
 380 mm | 14.961 in

 Depth, packed
 295 mm | 11.614 in

 Length, packed
 2778 mm | 109.37 in

 Weight, gross
 45.3 kg | 99.869 lb

Regulatory Compliance/Certifications

Agency Classification

CE Compliant with the relevant CE product directives

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

BSAMNT-3 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.

Kit contains one scissor top bracket set and one bottom bracket set.

BSAMNT-M – Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round

members. Kit contains one scissor bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



BSAMNT-3



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net6.2 kg | 13.669 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity

Weight, gross 6.4 kg | 14.11 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant







BSAMNT-M



Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net4.5 kg | 9.921 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity

Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



COMMSCOPE®