

SBNHH-1D85B



6-port sector antenna, 2x 698–896 and 4x 1695–2360 MHz, 85° HPBW, 3x RET

- Interleaved dipole technology providing for attractive, low wind load mechanical package
- Three internal RETs for independent tilt on all three bands
- The antenna is supplied with mounting kits that provide 0 degree of mechanical downtilt; optional downtilt mounting kits are available

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage Wind loading figures are validated by wind tunnel measurements described in white paper WP-112534-EN
Radome Material	Fiberglass, UV resistant
Radiator Material	Aluminum Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, high band	4
RF Connector Quantity, low band	2
RF Connector Quantity, total	6

Remote Electrical Tilt (RET) Information


RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Input Voltage	10–30 Vdc
Internal RET	High band (2) Low band (1)
Power Consumption, idle state, maximum	2 W
Power Consumption, normal conditions, maximum	13 W
Protocol	3GPP/AISG 2.0 (Multi-RET)

SBNHH-1D85B

Dimensions

Width	301 mm 11.85 in
Depth	180 mm 7.087 in
Length	1851 mm 72.874 in
Net Weight, without mounting kit	19.1 kg 42.108 lb

Array Layout



Array	Freq (MHz)	Conns	RET (MRET)	AISG RET UID
R1	698-896	1-2	1	ARxxxxxxxxxxxxxxxxxx.1
Y1	1695-2360	3-4	2	ARxxxxxxxxxxxxxxxxxx.2
Y2	1695-2360	5-6	3	ARxxxxxxxxxxxxxxxxxx.3

Left Bottom Right

(Sizes of colored boxes are not true depictions of array sizes)

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2360 MHz 698 – 896 MHz
Polarization	±45°

Electrical Specifications

Frequency Band, MHz	698–806	806–896	1695–1880	1850–1990	1920–2200	2300–2360
Gain, dBi	14.5	14.4	17	17.6	17.9	17.9
Beamwidth, Horizontal, degrees	82.5	86.1	81	79.3	79	79
Beamwidth, Vertical, degrees	12.3	11.1	5.7	5.3	5	4.6
Beam Tilt, degrees	0–12	0–12	0–8	0–8	0–8	0–8
USLS (First Lobe), dB	19	18	15	16	17	18
Isolation, Cross Polarization,	25	25	25	25	25	25

SBNHH-1D85B

dB

Isolation, Inter-band, dB	30	30	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	300	300	300	300	300	250

Electrical Specifications, BASTA

Frequency Band, MHz	698–806	806–896	1695–1880	1850–1990	1920–2200	2300–2360
Gain by all Beam Tilts, average, dBi	14.3	14.2	16.8	17.4	17.7	17.8
Gain by all Beam Tilts Tolerance, dB	±0.3	±0.5	±0.5	±0.3	±0.4	±0.3
Gain by Beam Tilt, average, dBi	0° 14.2 6° 14.3 12° 14.1	0° 14.1 6° 14.3 12° 13.9	0° 16.8 4° 16.8 8° 16.7	0° 17.5 4° 17.5 8° 17.2	0° 17.7 4° 17.8 8° 17.5	0° 17.6 4° 18.0 8° 17.6
Beamwidth, Horizontal Tolerance, degrees	±2.4	±1.7	±4.8	±3.2	±3.8	±1.9
Beamwidth, Vertical Tolerance, degrees	±0.6	±0.9	±0.2	±0.2	±0.3	±0.2
USLS, beampeak to 20° above beampeak, dB	16	14	15	16	17	18
Front-to-Back Total Power at 180° ± 30°, dB	22.5	23	27	26	25	27
CPR at Boresight, dB	20	20	23	22	18	22
CPR at Sector, dB	15	16	12	13	10	6

Mechanical Specifications

Effective Projective Area (EPA), frontal	0.27 m ² 2.906 ft ²
Effective Projective Area (EPA), lateral	0.22 m ² 2.368 ft ²
Wind Loading @ Velocity, frontal	283.0 N @ 150 km/h (63.6 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	234.0 N @ 150 km/h (52.6 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	545.0 N @ 150 km/h (122.5 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	287.0 N @ 150 km/h (64.5 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	380 mm 14.961 in
----------------------	--------------------

SBNHH-1D85B

Depth, packed	295 mm 11.614 in
Length, packed	1973 mm 77.677 in
Weight, gross	28 kg 61.729 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

BSAMNT-2F	-	Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.
-----------	---	--

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---