Diplexer, 1800-2100//2300-2600 MHz, dc bypass on 2300-2600 port

Product Classification

Product Type Diplexer

General Specifications

Product Family CBC1726

Color Gray

Common Port Label COMM

Modularity 1-Single

Mounting Pole | Wall

Mounting Pipe Hardware Band clamps (2)

RF Connector Interface 7-16 DIN Female

RF Connector Interface Body Style Medium neck

Dimensions

Height 152.4 mm | 6 in

Width 123 mm | 4.843 in


Depth 59 mm | 2.323 in

Ground Screw Diameter 6 mm | 0.236 in

Mounting Pipe Diameter Range 42.6–122 mm



Outline Drawing



Electrical Specifications

Impedance 50 ohm

License Band, Band Pass AWS 1700 | DCS 1800 | IMT 2100 | IMT 2600 | PCS 1900 | TDD

1900 | TDD 2000 | TDD 2300 | TDD 2600 | WCS 2300

Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through, combinerBranch 2dc/AISG Pass-through, demultiplexerBranch 2Lightning Surge Current3 kA

Lightning Surge Current Waveform 10/350 waveform




Electrical Specifications

Sub-module	1	1
Branch	1	2
Port Designation	1710-2170	2300-2690
License Band	AWS 1700, Band Pass DCS 1800, Band Pass	IMT 2600, Band Pass WCS 2300, Band Pass
	IMT 2100, Band Pass	TDD 2300, Band Pass
	PCS 1900, Band Pass	TDD 2600, Band Pass
	TDD 1900, Band Pass	
	TDD 2000 Band Pass	

Electrical Specifications, Band Pass

Frequency Range, MHz	1710-2170	2300-2690
Insertion Loss, maximum, dB	0.4	0.4
Insertion Loss, typical, dB	0.3	0.35
Total Group Delay, maximum, ns	30	30
Return Loss, minimum, dB	18	18
Return Loss, typical, dB	20	20
Isolation, minimum, dB	50	50
Input Power, PEP, maximum, W	3500	3500
3rd Order PIM, typical, dBc	-155	-155
3rd Order PIM Test Method	1 x 20 W AWS CW tone 1 x 20 W PCS CW tone	1 x 20 W AWS CW tone 1 x 20 W PCS CW tone

Block Diagram



Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Corrosion Test Method IEC 60068-2-11, 30 days
Ingress Protection Test Method IEC 60529:2001, IP67

Packaging and Weights

Included Mounting hardware

Volume 1.1 L

Weight, net 2.4 kg | 5.291 lb