## CPC3312

#### **Base Product**



### Product Classification

Regional Availability Portfolio Product Type Product Brand Product Series Ordering Note

### GigaSPEED XL® Cat 6 RJ45 Patch Cord, Non-Plenum

Asia   Australia/New Zealand   EMEA   Latin America   North America
SYSTIMAX®
Twisted pair patch cord
GigaSPEED XL®
CPC   UTG
Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords   Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices
б
U/UTP (unshielded)
Stranded
RJ45 plug
Standard

### General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface Feature, connector A	Standard
Interface, Connector B	RJ45 plug
Interface Feature, connector B	Standard
Jacket Color	Black   Blue   Darkgray   Green   Light blue   Lilac   Orange   Purple   Red   Spring green   Violet   White   Yellow
Pairs, quantity	4
Transmission Standards	IEEE 802.3bt Type 4
Wiring	T568B
Dimensions	
Cable Assembly Length Range (m)	1 - 30

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 29, 2023



# CPC3312

Cable Assembly Length Range (ft)	1 – 100
Cable Assembly Length Range (cm)	15 – 999
Cable Assembly Length Range (in)	6 – 999
Diameter Over Jacket	5.97 mm   0.235 in
Compatible Conductor Gauge, stranded	24 AWG

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

### Electrical Specifications

dc Resistance, maximum	0.3 ohm
Safety Voltage Rating	300 V


## Ordering Tree

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 29, 2023



# CPC3312



### 11 F Foot M Meter N Inch C Centimeter Length

 Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices

 Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

### Material Specifications

Contact Plating Material	Precious metals
Material Type	Copper alloy   Polycarbonate
Mechanical Specifications	
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   29.9 lbf

### **Environmental Specifications**

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Safety Standard	Anatel   ETL   cETL

### Packaging and Weights

Packaging quantity

1

### Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 29, 2023

**COMMSCOPE**<sup>®</sup>