CPPSSZ2

#### **Base Product**



# GigaSPEED X10D® 360GS10E Solid Low Smoke Zero Halogen Cordage Modular Patch Cord, Eco-Packaging

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	SYSTIMAX®
Product Type	Twisted pair patch cord
Product Brand	GigaSPEED X10D®
Product Series	CPP
Ordering Note	Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords   Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices

#### General Specifications

ANSI/TIA Category	6A
Cable Type	U/UTP (unshielded)
Conductor Type	Solid
Interface, Connector A	RJ45 plug
Interface Feature, connector A	Standard
Interface, Connector B	RJ45 plug
Interface Feature, connector B	Standard
Jacket Color	Black   Blue   Dark gray   Green   Light blue   Lilac   Orange   Red   Slate   Spring green   White   Yellow
Pairs, quantity	4
Transmission Standards	IEEE 802.3bt Type 4
Wiring	Т568В

#### Dimensions

Page 1 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 29, 2023



## CPPSSZ2

Cable Assembly Length Range (m)	1 – 30
Cable Assembly Length Range (ft)	4 - 100
Cable Assembly Length Range (cm)	100 – 999
Cable Assembly Length Range (in)	48 - 999
Diameter Over Jacket	7.24 mm   0.285 in
Compatible Conductor Gauge, solid	24 AWG

### Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

#### **Electrical Specifications**

dc Resistance, maximum	0.3 ohm
Safety Voltage Rating	300 V

### Ordering Tree

Page 2 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 29, 2023



## CPPSSZ2



#### • Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

#### Material Specifications

Contact Plating Material	Precious metals
Material Type	Copper alloy   Polycarbonate
Mechanical Specifications	
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   29.9 lbf

Blue

#### **Environmental Specifications**

-10 °C to +60 °C (+14 °F to +140 °F)
Low Smoke Zero Halogen (LSZH)
UL 94 V-0
ETL   cETL

#### Packaging and Weights

Packaging Material	Eco-friendly, single-use plastics-free
Packaging quantity	1

#### Regulatory Compliance/Certifications

Agency

Classification

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 29, 2023



### CPPSSZ2

CHINA-ROHS

ISO 9001:2015

**REACH-SVHC** 

ROHS

UK-ROHS



Below maximum concentration value Designed, manufactured and/or distributed under this quality management system Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant

Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 29, 2023

