810009309/DB /1X24AWG/SP29

810009309/DB | 0-001-DF-HY-F01NS/8G001

Universal Service Drop, tonable, with 900um buffer



 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Hybrid cable, fiber and tone-wire

Government FundingBuild America Buy America (BABA) compliant*

General Specifications

Cable Type Drop

Construction Type Non-armored

Fiber Short Description O-002-DF-HY-F02NS/IC29/1X24AWG

Subunit TypeGel-freeJacket ColorBlackSubunit, quantity1Fibers per Subunit, quantity1

Tone Wire, quantity 1

Total Fiber Count 1

Dimensions


Height Over Jacket4.572 mm0.18 inBuffer Tube/Subunit Diameter2.794 mm0.11 inDiameter Over Jacket9.906 mm0.39 in

Tone Wire Gauge 24 AWG

Representative Image



810009309/DB | 0-001-DF-HY-F01NS/8G001 /1X24AWG/SP29



Mechanical Specifications

Minimum Bend Radius, loaded91.44 mm | 3.6 inMinimum Bend Radius, unloaded63.5 mm | 2.5 inTensile Load, long term, maximum400.34 N | 90 lbf

 Tensile Load, short term, maximum
 1,334.466 N | 300 lbf

 Compression
 2.25 kg/mm | 126 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.17 ft lb | 2.942 N-m

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 1,071.677 m | 3516 ft

Optical Specifications

Fiber Type G.657.A2/B2 | G.657.A2/B2

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+167 \,^{\circ}\text{F}$)

Page 2 of 4



810009309/DB /1X24AWG/SP29

810009309/DB | 0-001-DF-HY-F01NS/8G001

Cable Qualification StandardsANSI/ICEA S-110-717

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penentration 24 h

Water Penentration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Drip 70 °C | 158 °F

Drip Test Method FOTP-81 | IEC 60794-1 E14

Heat Age $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ $(-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend -30 °C to +60 °C (-22 °F to +140 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 38.097 kg/km | 25.6 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

R-001-SP-8G-F29IV/WB – Fiber indoor cable, All-Dielectric Indoor Riser Simplex, Singlemode G.657.A2/B2, Feet jacket marking, Ivory jacket color

Page 3 of 4

810009309/DB | 0-001-DF-HY-F01NS/8G001 /1X24AWG/SP29

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 4 of 4