BC-30-10



Pipe-to-Pipe Clamp, heavy duty, joins two 1-1/2 in to 3-1/2 in OD round members

Product Classification

Product Type Clamp set

General Specifications

MountingPipe-to-pipeTower TaperTapered

Dimensions

 Height
 50.8 mm | 2 in

 Width
 152.4 mm | 6 in

 Length
 254 mm | 10 in

 Mounting Diameter, maximum
 88.9 mm | 3.5 in

 Mounting Diameter, minimum
 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

Weight, net 5.4 kg | 11.905 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



BC-30-10

UK-ROHS

Compliant





