GK-SUNV



Universal Grounding Kit for 1/4 in through 5/8 in cables

Product Classification	
Product Type	Grounding kit
Ordering Note	CommScope® standard product (Global)
General Specifications	
Bonding Conductor Jacketing Material	PVC
Bonding Conductor Material	Copper
Bonding Conductor Wire Size	10 gauge
Cable Type	Corrugated Smoothwall
Color	Black
Grounding Kit Type	Universal Grounding Kits
Grounding Strap Material	Tinned copper
Lug Attachment	Factory attached
Lug Туре	One-hole lug
Thread Size	M8
Dimensions	
Bonding Conductor Length	609.6 mm 24 in
Cable Jacketing Removal Length, maximum	58.42 mm 2.3 in

Cable Jacketing Removal Length, maximum	58.42 mm 2.3 in
Cable Jacketing Removal Length, minimum	55.88 mm 2.2 in
Compatible Diameter, maximum	15.24 mm 0.6 in
Compatible Diameter, minimum	2.54 mm 0.1 in
Nominal Size	1/2 in 1/4 in 3/8 in 5/8 in

Electrical Specifications

Page 1 of 7



GK-SUNV

Current Handling	Tested to withstand 30,000 amps peak current surge
Current Handling Test Method	MIL-STD-1757
Grounding, Bonding and Shielding Test Method	MIL-STD-188-124A
Lightning Protection Test Method	IEC 1024-1
Material Specifications	
Rivet Material	Copper
Environmental Specifications	
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Blowing Rain Test Method	MIL-STD-810, Method 506
Corrosion Test Method	MIL-STD-1344, Method 1001
Freezing Rain/Icing Test Method	MIL-STD-810, Method 521
Humidity Test Method	MIL-STD-1344, Method 1002
Immersion Test Method	IEC 60529:2001, IP68
UV Resistance Test Method	MIL-STD-810, Method 505
Vibration Test Method	MIL-STD-202, Method 214
Weatherproofing Method	Butyl and electric tape
Packaging and Weights	
Height, packed	152.4 mm 6 in
Width, packed	76.2 mm 3 in
Length, packed	58.42 mm 2.3 in
Included	Grounding kit Hardware Lug One roll of 2 in PVC tape One roll of 24 in butyl rubber tape
Packaging quantity	1
Weight, gross	0.28 kg 0.617 lb
Dogulatory Compliance/Costifications	

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 2 of 7



GK-SUNV

ROHS

UK-ROHS

Compliant Compliant



Included Products

42615-10 – Butyl Rubber Tape, 24 in 9905-71 – Black 2 in PVC Tape, 20 ft

* Footnotes

Grounding, Bonding and Shielding Test Method	Military Standard for Grounding, Bonding, and Shielding: Bond Resistance Requirement of a Maximum dc resistance of 0.001 ohm
Lightning Protection Test Method	Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02

Page 3 of 7



42615-10



Product Classification

Butyl Rubber Tape, 24 in

Weatherproofing tape
CommScope® non-standard product
Provides additional moisture seal for cable connections
One 1/2 in-2-1/4 in One 1/2 in-7/8 in One 1/2 in-7/8 in to device Two 1/2 in-1/2 in
Black
63.5 mm 2.5 in
609.6 mm 24 in
1-1/4 in 1-5/8 in 1/2 in 1/4 in 2-1/4 in 3/8 in 5/8 in 7 /8 in
Butyl rubber tape
Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 $^\circ\mathrm{F}$ then 4 hours of condensation at 104 $^\circ\mathrm{F}$
≥1000 hours
04AS00-03.6.0 MIL-STD-1344A, Method 1002
63.5 mm 2.5 in
63.5 mm 2.5 in 71.12 mm 2.8 in

Page 4 of 7



42615-10

Packaging quantity

1

Weight, gross

0.17 kg | 0.375 lb

Regulatory Compliance/Certifications

Classification

Agency

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 5 of 7



9905-71



Product Classification

Black 2 in PVC Tape, 20 ft

PIUUULI LIASSIIILALIUII		
Product Type	Weatherproofing tape	
Ordering Note	CommScope® non-standard product	
General Specifications		
Application	Provides additional moisture seal for cable connections	
Applications per Kit	Four 1/2 in–1/2 in Four 1/2 in–7/8 in to device One 1/2 in–2-1/4 in Two 1/2 in–7/8 in	
Color	Black	
Dimensions		
Width	50.8 mm 2 in	
Length	6096 mm 240 in	
Nominal Size	1-1/4 in 1-5/8 in 1/2 in 1/4 in 2-1/4 in 3/8 in 5/8 in 7/8 in	
Material Specifications		
Material Type	PVC tape	
Environmental Specifications		
UV Resistance Test Method	PVC tape test method UL 510, ASTM D1000	
Weather Resistance Test Method	04AS00-03.6.0 MIL-STD-1344A, Method 1002	
Packaging and Weights		
Height, packed	63.5 mm 2.5 in	
Width, packed	63.5 mm 2.5 in	
Length, packed	50.8 mm 2 in	
Packaging quantity	1	
Weight, gross	0.08 kg 0.176 lb	

Page 6 of 7



Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 7 of 7

